

Atellica Portfolio of Laboratory Products

Engineered by Siemens Healthineers to deliver control and simplicity so you can drive better outcomes.

Tighter control of your lab, simplified workflow, and more time to focus on driving better business and clinical outcomes—that's the promise of our Atellica® portfolio of laboratory products.

Control. Simplicity. Better Outcomes.

For use
in the
U.S.

Atellica Solution Test Menu



Immunoassay

Anemia

Active-B12
EPO
Ferritin
Folate
RBC Folate
Vitamin B12

Autoimmune

Anti-CCP IgG

Bone Metabolism

Intact PTH
Vitamin D Total

Cardiac

BNP
CKMB
High-Sensitivity Troponin I
Myoglobin
NT-proBNP II†

Diabetes

C-Peptide
Insulin

Growth

Growth Hormone (hGH)†
IGF-I†
IGFBP-3†

Hepatitis

Anti-HBe†
Anti-HBs 2
HAV IgM
HAV Total
HBc IgM
HBc Total
HBeAg
HBsAg II
HBsAg Confirmatory
HCV

HIV

HIV 1/O/2 Enhanced (EHIV)
HIV Ag/Ab Combo (CHIV)

Immunosuppressant Drugs

Cyclosporine
Everolimus†
Sirolimus†
Tacrolimus†

Inflammation

IgE, Total
IL2R†
TNFα†

Liver Disease

Enhanced Liver Fibrosis
(ELF™) Test

Metabolic

ACTH†
Cortisol
Homocysteine

Neurology

β-Amyloid 1-42 (AB42)†
Serum Neurofilament light
chain (sNfL)†
Total-Tau (TTAU)†

Oncology

AFP
BR 27.29
CA 125II™
CA 15-3™
CA 19-9™
Calcitonin
CEA
Complexed PSA
CYFRA 21-1†
Free PSA II†
PSA
Serum HER-2/neu

Reproductive Endocrinology

Androstenedione
Anti-Mullerian Hormone
(AMH)**
DHEA-SO4
Enhanced Estradiol
FSH
hCG
LH
PIGF†
Progesterone
Prolactin
sFlt-1†
SHBG
Testosterone II

Research Use Only

Free β-hCG
HBsAg II Quant
IL-6
PAPP-A

Sepsis

Procalcitonin (PCT)

Special ID

EBV-EBNA IgG†
EBV-VCA IgG†
EBV-VCA IgM†
SARS-CoV-2 Ag (CoVAg)**
SARS-CoV-2 IgG (sCOVG)††
SARS-CoV-2 Total (COV2T)††
Syphilis
Zika Test

Therapeutic Drug Monitoring

Digitoxin
Digoxin

Thyroid

Anti-TG
Anti-TPO
Free T3
Free T4
Thyroglobulin (Tg)†
Total T3
Total T4
TSH3-Ultra
T Uptake

TORCH

CMV IgG
CMV IgM†
Herpes-1 IgG
Herpes-2 IgG
Rubella IgG
Rubella IgM
Toxoplasma IgG
Toxoplasma IgM

†Under development. Not commercially available. Future availability cannot be guaranteed.

§CA 125II, CA 15-3, and CA 19-9 are trademarks of Fujirebio Diagnostics, Inc.

**Under FDA review. Not available for sale in the U.S.

††This test has not been FDA cleared or approved. This test has been authorized by FDA under an EUA for use by authorized laboratories. This test has been authorized only for detecting the presence of antibodies against SARS-CoV-2, not for any other viruses or pathogens. This test is only authorized for the duration of the declaration that circumstances exist justifying the authorization of emergency use of in vitro diagnostics for detection and/or diagnosis of COVID-19 under Section 564(b)(1) of the Act, 21 U.S.C. § 360bbb-3(b)(1), unless the authorization is terminated or revoked sooner. Product availability may vary by country and is subject to varying regulatory requirements.

Atellica, ELF, and all associated marks are trademarks of Siemens Healthcare Diagnostics Inc., or its affiliates. All other trademarks and brands are the property of their respective owners.

Product availability may vary from country to country and is subject to varying regulatory requirements.

Contact your Fisher Healthcare representative to learn more.

Distributed by Fisher Healthcare. Contact us today:

In the United States

Order online: fisherhealthcare.com

Call customer service: 1-800-640-0640



© 2023 Thermo Fisher Scientific Inc. All rights reserved.

Trademarks used are owned as indicated at fishersci.com/trademarks.

BN235868254-US



siemens-healthineers.com

Published by Siemens Healthcare Diagnostics Inc.

Laboratory Diagnostics

Tarrytown, NY 10591-5005 USA