

Keeping it cool with sample storage

Help protect and preserve your precious samples with our extensive portfolio of capable and reliable cold storage solutions.

Thermo Scientific™ refrigerators, freezers, and ultra-low temperature (ULT) freezers

Product description	Cat. No.
TSX Series ultra-low temperature freezers	
400-box capacity, 115V, 60 Hz	TSX40086A
400-box capacity, 208–230V, 60 Hz	TSX40086D
500-box capacity, 115V, 60 Hz	TSX50086A
500-box capacity, 208–230V, 60 Hz	TSX50086D
600-box capacity, 115V, 60 Hz	TSX60086A
600-box capacity, 208–230V, 60 Hz	TSX60086D
700-box capacity, 115V, 60 Hz	TSX70086A
700-box capacity, 208–230V, 60 Hz	TSX70086D
TDE Series ultra-low temperature freezers	
400-box capacity, 115V, 60 Hz	01257916
400-box capacity, 208–230V, 60 Hz	01257917
600-box capacity, 115V, 60 Hz	01257932
600-box capacity, 208–230V, 60 Hz	01257933
500-box capacity, 208–230V, 60 Hz	01257925
TSX Series high-performance freezers and refrigerators	
Solid door, –30°C auto defrost, 23 cu. ft., 115V, 60 Hz	
Solid door, –20°C auto defrost, 23 cu. ft., 115V, 60 Hz	TSX2320FA
Glass door, 23 cu. ft., 115V, 60 Hz	TSX2305GA
Solid door, 23 cu. ft., 115V, 60 Hz	TSX2305SA
Undercounter design, single glass door, 5.5 cu. ft., 100–240V, 50–60 Hz	TSX505GA
Undercounter design, single solid door, 5.5 cu. ft., 100–240V, 50–60 Hz	TSX505SA



Thermo Scientific™ Matrix™ storage tubes

Product description	Cat. No.
V-bottom 1.0 mL ScrewTop tubes, 5 racks of 96/case, colorless	14754558
V-bottom 1.0 mL ScrewTop tubes, 5 racks of 96/case	14754563
1.0 mL barcoded ScrewTop tubes, 5 racks of 96/case	14754574
0.5 mL ScrewTop Tubes in barcoded latch racks	14754598
0.5 mL ScrewTop tri-coded tubes	14754610
1.0 mL ScrewTop tri-coded tubes	14754556
ScrewTop tube cap tray, case of 480, colorless	14754667
ScrewTop tube cap tray, case of 480, purple	14754682



Check out our full selection of [Thermo Scientific Matrix storage tubes](#).

Thermo Scientific™ F1-ClipTip™ variable volume single channel pipettes

Product description	Cat. No.
1–10 µL	04100513
2–20 µL	14488014N
5–50 µL	14488015N
10–100 µL	14488016N
30–300 µL	14488018N



Thermo Scientific™ E1-ClipTip™ electronic adjustable tip spacing multichannel equalizer pipettes

Product description	Cat. No.
8-channels, 2–125 µL, Bluetooth™ technology (compatible with ClipTip 200 µL tips)	14387966BT
8-channels, 15–1,250 µL, Bluetooth technology	14387957BT
8-channels, 2–125 µL, Bluetooth technology (compatible with ClipTip 384 µL and 12.5 µL tips)	14387971BT
12-channels, 0.5–12.5 µL, Bluetooth technology	14387972BT
12-channels, 2–125 µL, Bluetooth technology	14387974BT



Thermo Scientific™ Nunc™ storage plates

Product description	Cat. No.
Thermo Scientific™ Nunc™ 96-well polypropylene DeepWell™ storage plates	
Natural, round bottom, sterile, barcode	12565395
Natural, round bottom, non-sterile, barcode	12565394
Natural, V-bottom, non-sterile, barcode, 2,000 µL	12565650
Natural, V-bottom, non-sterile, 450 µL	12565436
Thermo Scientific™ Nunc™ 96-well polypropylene storage microplates	
Natural, U-shape bottom, non-sterile, 450 µL	12565368
Natural, U-shape bottom, non-sterile, barcode, 2,000 µL	12565606



Thermo Scientific™ TSV Value convertible freezers/refrigerators

Product description	Cat. No.
General purpose freezer (convertible to refrigerator)	TSV20FPSA
General purpose refrigerator (convertible to freezer)	TSV20RPSA
Undercounter refrigerator	TSV05RPSA
Value lab upright freezer	05LFEETSA



Thermo Scientific™ XBF40D blast freezers

Product description	Cat. No.
Thermo Scientific™ XBF40D –40°C Blast Freezer	
Thermo Scientific™ XBF40D-MD –40°C Blast Freezer for Plasma	



Thermo Scientific™ screw cap microcentrifuge tubes

Product description	Cat. No.
2 mL, natural, sterile	21403201
1.5 mL, natural, sterile	14755287



Thermo Scientific™ snap cap low retention microcentrifuge tubes

Product description	Cat. No.
1.5 mL, natural, non-sterile	21402902
2.0 mL, natural, sterile	21402904



Learn more at thermofisher.com/furl