



Instruments on the bench in nearly every lab

Explore a wide range of high-quality, trusted instruments for your everyday needs in the lab

Electrochemistry: Bench meters

Description	Cat. No.
Thermo Scientific™ Orion™ Lab Star bench meters	
PH111 pH Bench Meter Standard Kit	15200968
PH111 pH/mV Bench Meter Difficult Sample Kit	15200971
EC112 Conductivity Bench Meter Standard Kit	15200973
Thermo Scientific™ Orion Star™ benchtop pH meters	
A211 Benchtop pH Meter	13645521
A215 pH/Conductivity Benchtop Multiparameter Meter	13645547



Thermo Scientific™ Sorvall™ Legend™ microcentrifuges

Description	Cat. No.
Micro 17 Microcentrifuge, 120 V, 60 Hz	75002431
Micro 21 Microcentrifuge, 120 V, 60 Hz	75002436
Micro 17R Microcentrifuge, 120 V, 60 Hz	75002441
Micro 21R Microcentrifuge, 120 V, 60 Hz	75002446



Thermo Scientific™ F1-ClipTip™ Variable Volume Single Channel Pipettes

Description	Cat. No.
1–10 µL	04100513
2–20 µL	14488014N
5–50 µL	14488015N
10–100 µL	14488016N
30–300 µL	14488018N



Thermo Scientific™ rockers, rotators, and mixers

Description	Cat. No.
Digital Platform Rocker	88882013
Digital Tube Rocker	88882017
Digital Mini Rotator	88882007
Tube Revolver Rotator	88881001
Digital Waving Rotator	88882003
Digital Vortex Mixer	88882009
Basic Vortex Mixer	88882011



Storage plates

Description	Cat. No.
Thermo Scientific™ Nunc™ 96-Well Polypropylene DeepWell™ Storage Plates	
Natural, U-bottom, sterile, barcode	12565395
Natural, U-bottom, nonsterile, barcode	12565394
Natural, V-bottom, nonsterile, barcode, 2,000 µL	12565650
Natural, U-bottom, nonsterile, barcode, 2,000 µL	12565606
Thermo Scientific™ Nunc™ 96-Well Polypropylene Storage Microplates	
Natural, V-bottom, nonsterile, 450 µL	12565436
Natural, U-bottom, nonsterile, 450 µL	12565368



Thermo Scientific™ Screw Cap Micro Tubes

Description	Cat. No.
2 mL, natural, sterile	21403201
1.5 mL, natural, sterile	14755287



Thermo Scientific™ Snap Cap Low Retention Microcentrifuge Tubes

Description	Cat. No.
1.5 mL, natural, nonsterile	21402902
2.0 mL, natural, nonsterile	21402904



Pipettes, tips, and racks

Description	Cat. No.
Thermo Scientific™ SoftFit-L™ pipette tips in hinged racks, 20 µL	
Filtered, sterile	21402550
Nonfiltered, sterile	21402552
Nonfiltered, nonsterile	21402554
Filtered, low retention, sterile	21402551
Nonfiltered, low retention, sterile	21402553
Nonfiltered, low retention, nonsterile	21402555
SoftFit-L pipette tips in hinged racks, 200 µL	
Filtered, sterile	21402561
Nonfiltered, sterile	21402563
Nonfiltered, nonsterile	21402565
Filtered, low retention, sterile	21402562
Nonfiltered, low retention, sterile	21402564
Nonfiltered, low retention, nonsterile	21402566
SoftFit-L pipette tips in hinged racks, 300 µL	
Filtered, sterile	21402571
Nonfiltered, sterile	21402573
Nonfiltered, nonsterile	21402575
Filtered, low retention, sterile	21402572
Nonfiltered, low retention, sterile	21402574
Nonfiltered, low retention, nonsterile	21402576
SoftFit-L pipette tips in hinged racks, 1,000 µL	
Filtered, sterile	21402581
Nonfiltered, sterile	21402583
Nonfiltered, nonsterile	21402585
Filtered, low retention, sterile	21402582
Nonfiltered, low retention, sterile	21402584
Nonfiltered, low retention, nonsterile	21402586
SoftFit-L pipette tips in hinged racks, 1,200 µL	
Filtered, sterile	21402592
Nonfiltered, sterile	21402594
Nonfiltered, nonsterile	21402596
Filtered, low retention, sterile	21402593



Pipettes, tips, and racks (continued)

Description	Cat. No.
Thermo Scientific™ Finnpiquette™ F1 Variable Volume Pipettes	
1–10 µL	14386302N
2–20 µL	14386305N
10–100 µL	14386306N
20–200 µL	14386307N
100–1,000 µL	14386309N
Thermo Scientific™ Finnpiquette™ F1 Multichannel Pipettes	
1–10 µL	14386349N
10–100 µL	14386351N
30–300 µL	14386352N
Thermo Scientific™ ART™ pipette tips	
Barrier Specialty Pipette Tips	14386300N
Barrier Extended Length Pipette Tips	14386302N
Barrier Pipette Tips in Hinged Racks, 10 µL	14386306N
Barrier Pipette Tips in Hinged Racks, 20 µL	14386352N
Barrier Pipette Tips in Hinged Racks, 100 µL	14386351N
Barrier Pipette Tips in Hinged Racks, 200 µL	14386305N
Nonfiltered Standard Hinged Rack Pipette Tips	13811103

 Learn more at thermofisher.com/furl

thermo scientific