Alfa Aesar



Alfa Aesar[™], now part of Thermo Fisher Scientific[™], is a leading manufacturer and supplier of research chemicals with a long and proud tradition of producing organic compounds for the drug discovery and agrochemical markets. Our comprehensive range of organic molecules allows our customers to conduct a broad range of synthetic chemistry methodologies and enables them to facilitate their research and development projects.

The following list of categories provides some examples of the broad range of organic synthesis products available:

General lab work essentials

- Solvents
- Organic acids, bases and salts
- Deuterated solvents

Functional reagents

- Organometallic compounds
- Halogenating agents
- Oxidizing and reducing agents
- Coupling reagents
- Alkylating reagents
- Ligands
- Protection and deprotection reagents
- Ionic liquids
- Phase transfer catalysts
- Silylating agents and silanes

Building blocks

- Heterocycles
- Boronic acids
- Alkanes
- Alkenes
- Acetylenes
- Aldehydes
- Hydroxyls
- Ethers
- Ketones
- Organo halides
- Carboxylic acids and derivatives
- Sulfonyl chlorides
- Sulfonamides
- Chiral compounds

To place an order contact your local Fisher Scientific office or order online at **fishersci.com/alfaaesar**



Organics

A selection of our organics products can be found in the table below.

Stock No.	Description	Size
AA41547	1-Methoxy-2-propanol, 99+%	250ml, 1L, 4L, 4x4L
AAL16584	1H,1H,2H,2H-Perfluorodecyltrichlorosilane, 96%	1g, 5g, 25g
AAB20156	1H,1H,2H,2H-Perfluorooctanol, 97%	10g, 50g, 250g
AA43142	2,3-Dimethylbutane, 98+%	50ml, 250ml, 1L
AAA17145	2,4,6-Triiodophenol, 98%	5g, 25g, 100g
AAA16893	Dimethyl sulfoxide-d_6, 99.5% (Isotopic)	10g, 50g
AAA16205	Glycerol, 99+%	500ml, 2.5L, 10L
AAL02161	Hexaethylene glycol, 96%	5g, 25g
AAL16519	Hexamethyldisilazane, electronic grade, 99+%	25ml, 100ml, 500ml
AAL14511	Methacryloyl chloride, may contain up to ca. 15% cyclic dimer, 97%, stab.	25g, 100g, 500g
AAA14732	n-Decane, 99%	100ml, 500ml, 2.5L
AAA14834	n-Dodecane, 99+%	100ml, 500ml, 2.5L
AAA10322	n-Hexadecane, 99%	100ml, 500ml, 2.5L
AAL09938	n-Hexane, 99%	50ml, 250ml, 1L
AAA12033	N,O-Bis(trimethylsilyl)trifluoroacetamide, 98+%	5g, 10g, 50g, 100g
AA43368	Paraformaldehyde, 16% w/v aq. soln., methanol free	2x10ml, 10x10ml
AAA12442	Piperidine, 99%	100ml, 500ml, 2.5L
AAA12704	Potassium iodide, 99%	50g, 250g, 1kg, 5kg
AAA10917	Sodium 1-heptanesulfonate, 99% (dry wt.), water <2%	5g, 25g, 100g
AA15764	Sodium 1-octanesulfonate monohydrate, 99+%	10g, 50g
AAA14292	Sodium 1-octanesulfonate, 99%	5g, 25g, 100g
AAA18346	Sodium taurocholate hydrate, 97%	1g, 5g, 25g
AAA19560	Thiamine hydrochloride, 99% (dry wt.), may contain. up to 5% water	100g, 250g, 1kg
AAA12198	Trifluoroacetic acid, 99%	100g, 500g, 2.5kg
AAA14894	Vitamin B12, 98+% (dry wt basis)	1g, 5g, 25g

Full product listing is available online.

To place an order contact your local Fisher Scientific office or order online at **fishersci.com/alfaaesar**



In the United States

For customer service, call 1-800-766-7000 To fax an order, use 1-800-926-1166 To order online: www.fishersci.com

In Canada

For customer service, call 1-800-234-7437 To fax an order, use 1-800-463-2996 To order online: www.fishersci.ca

For Research Use Only. Not for use in diagnostic procedures. © 2016 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified.

