

RELIABLE SAFETY SOLUTIONS YOU CAN TRUST DESIGNED FOR FACILITIES

Ansell is your safety partner when identifying hazards and injury risks associated with each task and equipping facility workers with the right solution from our extensive portfolio of hand and body protection. Whether facing risk of cut, impact, abrasion, electrical shock, burn, chemical splash, or other hazards, Ansell can help you reduce on-the-job injuries and deliver the comfort, performance, and protection needed to keep your facilities and workers safe and productive throughout the day.



AlphaTec® 1800 STANDARD Bound - Model 111

Lightweight, breathable microporous laminate technology, Type 5/6 protection

- Protects against low-hazard liquid spray and fine particulates
- Comfortable to wear featuring moisture vapor permeable fabric ("breathable") to help reduce the risk of heat stress
- Optimized body fit, improving wearer comfort and safety
- Anti-static, tested according to EN 1149-5 and AATCC 76
- Low linting to help reduce the risk of cross contamination in critical areas
- · Silicone-free, critical in spray painting applications









		5
	00000	
4		

ActivArmr® 80-813

Comfortable flame-resistant gloves, offering advanced arc flash and cut protection

- Flame-resistant materials: Satisfies CGSB 155.20-2000 FR standards
- Arc flash-resistant design: ASTM F2675-13 Category 2 protection*
- Cut-resistant DuPont™ Kevlar® yarn: Advanced cut protection

*Arc Rating (ATPV) = 9.4 cal/cm2 Arc Category Level 2 per ASTM F2675-13









6	[19-823-450]
8	[19-823-452]
9	[19-823-453]
10	[19-823-454]
11	[19-823-455]

[17-999-980]

[17-999-981]

[17-999-982]

[17-999-983]

[17-999-984]

[17-999-985]

[17-999-986]

[17-999-987]

2XL

3XL

4XL

5XL

HyFlex® 11-840

Durable industrial gloves, offering 2x more grip and up to 20% greater abrasion protection*

- FORTIX™ Abrasion Resistance: 2x more grip, up to 20% more durability*
- ERGOFORM™ Ergonomic Design: Reduced strain, better ergonomics

*vs. previous technology version









6	[19-010-338]
7	[19-010-339]
8	[19-010-340]
9	[19-010-341]
10	[19-010-342]
11	[19-010-343]

Consult AnsellGUARDIAN® Partner for glove and suit selection tailored to your unique set of chemicals, needs, and applications

Request an assessment



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. © 2022 Ansell Limited. All Rights Reserved.

Distributed by Fisher Scientific. Contact us today:

In the United States

Order online: fishersci.com
Fax an order: 1-800-926-1166
Call customer service: 1-800-766-7000

