

CONTACT US TODAY FOR FREE SAMPLES!

Fisher Sales Rep:

Fisher Safety Specialist:

2024 GLOVE PRICING

RoyalTouch300™ Nitrile Exam Gloves



- Strongest film possible with ultimate tactile sensitivity
- 300-count box saves space and reduces waste
- Finger-textured for a secure grip

Size	Hourglass Item No.	Fisher Scientific Cat. No.	Price
XS	300	18-041-140	
S	301	18-041-141	
M	302	18-041-142	
L	303	18-041-143	
XL*	304	18-041-144	

Packaging: 300 Pcs/Box; 10 Box/Case *XL 250 Pcs/Box

Typical Thickness: Palm 2.3 - 2.7 mil; Finger 3.9 - 4.3 mil

Scion700™ Nitrile Exam Gloves



Patented Technology*



Low Dermatitis Potential

NO Accelerators

- Accelerator-free **LOW DERMA™** technology nitrile* reduces your risk of developing allergic contact dermatitis
- 300-count box saves space and reduces waste
- Finger-textured for a secure grip

Size	Hourglass Item No.	Fisher Scientific Cat. No.	Price
XS	700	17-900-912	
S	701	17-900-913	
M	702	17-900-914	
L	703	17-900-915	
XL	704	17-900-916	

Packaging: 300 Pcs/Box; 10 Box/Case *XL 250 Pcs/Box

Typical Thickness: Palm 2.3 - 2.7 mil; Finger 3.9 - 4.7 mil

Sable600™ Nitrile Exam Gloves



Patented Technology*



Low Dermatitis Potential

NO Accelerators

- Accelerator-free **LOW DERMA™** technology nitrile* reduces your risk of developing allergic contact dermatitis
- 300-count box saves space and reduces waste
- Finger-textured for a secure grip

Size	Hourglass Item No.	Fisher Scientific Cat. No.	Price
XS	600	17-010-396	
S	601	17-010-397	
M	602	17-010-398	
L	603	17-010-399	
XL	604	17-010-400	

Packaging: 300 Pcs/Box; 10 Box/Case *XL 250 Pcs/Box

Typical Thickness: Palm 2.3 - 2.7 mil; Finger 3.9 - 4.7 mil

Fortis500™ Extended Cuff Nitrile Exam Gloves



- Chemo Tested
- Low Dermatitis Potential
- NO Accelerators
- NFPA 1999

- Accelerator-free LOW DERMA™ technology nitrile* reduces your risk of developing allergic contact dermatitis
- Thicker than standard exam gloves for increased durability, puncture resistance, and chemical protection.
- Extended cuff for extra wrist protection

Size	Hourglass Item No.	Fisher Scientific Cat. No.	Price
XS	500	17-900-927	
S	501	17-900-928	
M	502	17-900-929	
L	503	17-900-930	
XL	504	17-900-931	
XXL	505	17-900-932	

Packaging: 100 Pcs/Box; 10 Box/Case *XXL 90 Pcs/Box
Typical Thickness: Palm 3.5 - 3.9 mil; Finger 5.1 - 5.5 mil

FreeStyle1100™ Nitrile Exam Gloves



- Chemo Tested
- Low Dermatitis Potential
- NO Accelerators

- Accelerator-free LOW DERMA™ technology nitrile* reduces your risk of developing allergic contact dermatitis
- Ultra-low surfactants and finger-textured for a noticeably better wet grip

Size	Hourglass Item No.	Fisher Scientific Cat. No.	Price
XXS	1106	19-423-016	
XS	1100	19-423-006	
S	1101	19-423-007	
M	1102	19-423-008	
L	1103	19-423-009	
XL	1104	19-423-010	
XXL	1105	15-423-050	

Packaging: 100 Pcs/Box; 10 Box/Case *XXL 80 Pcs/Box

Typical Thickness: Palm 2.3 - 2.7 mil; Finger 3.9 - 5.1 mil



AQUA1900™ Nitrile Gloves | Non-Medical

Size	Hourglass Item No.	Fisher Scientific Cat. No.	Price
S	1901	19-423-038	
M	1902	19-423-039	
L	1903	19-423-040	
XL	1904	19-423-041	

Pkg: 100 Pcs/Box; 10 Box/Case Typical Thickness: Finger 4.7 - 5.5mil

* Patent www.lowerderma.com/patents

Distributed by Fisher Scientific. Contact us today:

In the United States

Order online: fishersci.com

Call customer service: 1-800-766-7000

© 2022 Thermo Fisher Scientific Inc. All rights reserved.

Trademarks used are owned as indicated at fishersci.com/trademarks.



HandPRO® 400 Latex Exam Gloves

Size	Hourglass Item No.	Fisher Scientific Cat. No.	Price
XS	400	180-401-251	
S	401	180-401-252	
M	402	180-401-253	
L	403	180-401-254	
XL	404	180-401-255	

Pkg: 100 Pcs/Bx; 10 Bx/CS (XL 800/Bx) Thickness: Finger 5.9 - 6.3mil

