

Improve the Sustainability of Your Lab

Recycle Your Pipette Tips and Racks

Thermo Scientific ART™, ART Barrier, and SoftFit-L™ Pipette Tips in Hinged Racks can help you meet your environmental goals. They're available as part of a mail-back recycling program that includes TipCycle Recycle Kits with select products. The kits make it as easy as 1- 2 - 3 to recycle used tips and racks.*

1. Kits will arrive with your order. Remove products and place the bag liner from the kit into the shipping container.
2. After use, collect and place your non-biohazardous tips and racks into the bag liner until full.
3. Seal the bag and container, insert a signed waiver, attach the prepaid shipping label, and send for recycling.

Contact your **Fisher Scientific sales representative** for details about participating in the program.

* Recycled products must be free of liquids, biohazards, and hazardous chemicals as defined by Title 40 of the Code of Federal Regulations (CFR), Part 261, or Regulated Medical Waste as defined by Title 49 of the CFR.

Tips and racks available with TipCycle Recycle Kits

ART Barrier Filtered Sterile Pipette Tips in Hinged Racks

Volume	Length	Low Retention	Cat. No.	Mfr. No.
10 µL	Standard	√	02-681-544	2139RC-05-HR
10 µL	Standard		02-681-573	2139RC-HR
10 µL	Extended		02-681-574	2140RC-HR
10 µL	Extended	√	02-681-545	2140RC-05-HR
20 µL	Standard		02-681-577	2149PRC-HR
20 µL	Standard	√	02-681-546	2149PRC-05-HR
100 µL	Standard		02-681-540	2065ERC-HR
100 µL	Standard	√	02-681-539	2065ERC-05-HR
200 µL	Extended		02-681-576	2069RC-HR
200 µL	Standard	√	02-681-541	2069RC-05-HR
1,000 µL	Standard		02-681-575	2179RC-HR
1,000 µL	Extended	√	02-681-547	2179RC-05-HR
1,000 µL	Extended		02-681-543	2079RC-HR
1,000 µL	Extended	√	02-681-542	2079RC-05-HR

ART Non-Filtered Sterile Pipette Tips in Hinged Racks

Volume	Length	Low Retention	Cat. No.	Mfr. No.
10 µL	Standard	√	02-681-555	3501RC-05-HR
10 µL	Standard		02-681-556	3501RC-HR
10 µL	Extended		02-681-558	3511RC-HR
10 µL	Extended	√	02-681-557	3511RC-05-HR
10 µL	Extended	√	02-681-559	3521RC-05-HR
20 µL	Extended		02-681-560	3521RC-HR
200 µL	Standard		02-681-562	3551RC-HR
200 µL	Standard	√	02-681-561	3551RC-05-HR
1,000 µL	Standard	√	02-681-553	3101RC-05-HR
1,000 µL	Extended		02-681-554	3101RC-HR

SoftFit-L Pipette Tips in Hinged Racks

Volume	Length	Sterile	Filtered	Cat. No.	Mfr. No.
20 µL	Standard	√	√	02-681-549	2749RC-HR
20 µL	Standard	√		02-681-563	3721RC-HR
20 µL	Standard			02-681-564	3722RC-HR
200 µL	Standard	√	√	02-681-550	2769RC-HR
200 µL	Standard	√		02-681-569	3751RC-HR
200 µL	Standard			02-681-570	3752RC-HR
300 µL	Standard	√	√	02-681-548	2739RC-HR
300 µL	Standard	√		02-681-565	3731RC-HR
300 µL	Standard			02-681-566	3732RC-HR
1,000 µL	Standard	√	√	02-681-551	2779RC-HR
1,000 µL	Standard	√		02-681-571	3781RC-HR
1,000 µL	Standard			02-681-572	3782RC-HR
1,200 µL	Standard	√	√	02-681-552	2789RC-HR
1,200 µL	Standard			02-681-568	3742RC-HR
1,200 µL	Standard	√		02-681-567	3741RC-HR

Visit fishersci.com to shop and learn more.

Distributed by Fisher Scientific. Contact us today:

In the United States

Order online: fishersci.com

Call customer service: 1-800-766-7000

