MagMAX kit and KingFisher instrument selection guide







Total RNA*



Blood

Applied Biosystems[™] MagMAX[™] for Stabilized Blood RNA Isolation Kit, Tempus[™] Tubes (Cat. No. 44-518-93)

Applied Biosystems[™] MagMAX[™] for Stabilized Blood RNA Isolation Kit, Paxgene[™] Tubes (Cat. No. 44-518-94)

Applied Biosystems[™] MagMAX[™] *mir*Vana[™] Total RNA Isolation Kit (Cat. No. A27828)



Plant tissue

Applied Biosystems[™] MagMAX[™] Plant RNA Isolation Kit (Cat. No. A33784)



Tissue (non-plant)



Cell culture


Applied Biosystems[™] MagMAX[™] *mir*Vana[™] Total RNA Isolation Kit (Cat. No. A27828)

^{*} Excludes small RNA.



True total RNA

(micro and large)




^{*} FFPE = formalin-fixed paraffin-embedded

Kit guide for Thermo Scientific™ KingFisher™ systems **thermofisher.com/kingfisherkits**



mRNA

(polyadenylated selected)



Kit guide for KingFisher systems **thermofisher.com/kingfisherkits**



DNA

	Plasma or serum
	FFPE
	Plant tissue
3.22 3.62	Feces
	Saliva
6	Blood
	Tissue (non-plant)
	Cell culture
	Buccal swab
	Other swabs

Applied Biosystems[™] MagMAX[™] Cell-Free DNA Isolation Kit (Cat. No. A29319)

Applied Biosystems[™] MagMAX[™] FFPE DNA/RNA Ultra Kit (Cat. No. A31881)

Applied Biosystems[™] MagMAX[™] Plant DNA Isolation Kit (Cat. No. A32549)

Applied Biosystems[™] MagMAX[™] Microbiome Ultra Nucleic Acid Isolation Kits (Cat. Nos. A42357, A42358)

Applied Biosystems[™] MagMAX[™] Saliva gDNA Isolation Kit (Cat. No. A39059)


Applied Biosystems[™] MagMAX[™] DNA Multi-Sample Ultra 2.0 Kit (Cat. No. A36570)

Thermo Scientific™ KingFisher™ Ready DNA Ultra 2.0 Prefilled Plates (Cat. No. FERA36586)

Thermo Scientific[™] KingFisher[™] Duo-Ready DNA Ultra 2.0 Prefilled Plates (Cat. No. FERA36584)



Viral, fungal, and bacterial RNA/DNA



Applied Biosystems[™] MagMAX[™] Pathogen RNA/DNA Kit (Cat. No. 44-623-59)

Applied Biosystems[™] MagMAX[™] Viral/Pathogen Ultra Nucleic Acid Isolation Kit (Cat. No. A42356)

Applied Biosystems[™] MagMAX[™] Viral/Pathogen Nucleic Acid Isolation Kit (Cat. No. A42352)

Applied Biosystems[™] MagMAX[™] Viral/Pathogen II Nucleic Acid Isolation Kit (Cat. No. A48383R)

Invitrogen[™] Dynabeads[™] Intact Virus Enrichment (optimized for SARS-CoV-2) (Cat. Nos. 10-700-D, 10-701-D)

Invitrogen™ Intact Virus Precipitation Reagent (optimized for SARS-CoV-2) (Cat. No. 10-720-D)



Total nucleic acid



Plasma or serum Applied Biosystems[™] MagMAX[™] Cell-Free Total Nucleic Acid Isolation Kit



Urine

Applied Biosystems[™] MagMAX[™] Cell-Free Total Nucleic Acid Isolation Kit (Cat. No. A36716)

Applied Biosystems[™] MagMAX[™] Microbiome Ultra Nucleic Acid Isolation Kits



Feces



Saliva



Viral transport media (VTM)



Fungi



Soil



Wastewater (sludge and sewage)

Applied Biosystems[™] MagMAX[™] Microbiome Ultra Nucleic Acid Isolation Kits

(Cat. Nos. A42357, A42358)

Applied Biosystems[™] MagMAX[™] Wastewater Ultra Nucleic Acid Isolation Kits (Cat. Nos. A52606, A52610)



Cell isolation

Positive cell isolation

Negative cell isolation

Depletion with Dynabeads products

Invitrogen[™] Dynabeads[™] FlowComp[™] Human CD4 Kit (Cat. No. 11-361-D)


Invitrogen[™] Dynabeads[™] FlowComp[™] Human CD14 Kit (Cat. No. 11-367-D)

Invitrogen[™] Dynabeads[™] FlowComp[™] Mouse CD4 Kit (Cat. No. 11-461-D)

Invitrogen[™] Dynabeads[™] FlowComp[™] Mouse CD8 Kit (Cat. No. 11-462-D)

Invitrogen[™] Dynabeads[™] Untouched[™] Human CD8 T Cells Kit (Cat. No. 11-348-D)

Invitrogen[™] Dynabeads[™] CD14 (Cat. No. 11-149-D)
Invitrogen[™] Dynabeads[™] CD19 Pan B (Cat. No. 11-143-D)



Protein isolation immunoprecipitation

Magnetic beads coated with Protein A or G

Magnetic beads coated with secondary antibodies

Magnetic beads coated with streptavidin

Invitrogen[™] Dynabeads[™] Protein A for Immunoprecipitation (Cat. No. 10-002-D)

Invitrogen[™] Dynabeads[™] Protein A Immunoprecipitation Kit (Cat. No. 10-006-D)

Invitrogen[™] Dynabeads[™] Protein G for Immunoprecipitation (Cat. No. 10-004-D)

Invitrogen[™] Dynabeads[™] Protein G Immunoprecipitation Kit (Cat. No. 10-007-D)

Thermo Scientific™ Pierce™ Protein A/G Magnetic Beads (Cat. No. Pl88803)

Invitrogen[™] Dynabeads[™] His-Tag Isolation and Pulldown (Cat. No. 10-104-D)

Invitrogen[™] Dynabeads[™] M-280 Sheep Anti-Mouse IgG (Cat. No. 11-202-D)

Invitrogen[™] Dynabeads[™] M-280 Sheep Anti–Rabbit IgG (Cat. No. 11-204-D)

Invitrogen[™] Dynabeads[™] M-280 Streptavidin (Cat. No. 11-206-D)
Thermo Scientific[™] Pierce[™] Streptavidin Magnetic Beads
(Cat. No. Pl88816)



KingFisher instruments



Thermo Scientific[™] KingFisher[™] Apex Purification System with 96 PCR Head (Cat. No. 54-009-10)

Thermo Scientific™ KingFisher™ Apex Purification System with 96 Combi Head (Cat. No. 54-009-20)

Thermo Scientific[™] KingFisher[™] Apex Purification System with 96 Deep-Well Head (Cat. No. 54-009-30)

Thermo Scientific[™] KingFisher[™] Apex Purification System with 24 Combi Head (Cat. No. 54-009-40)



Flex*

Thermo Scientific™ KingFisher™ Flex Purification System with 96 PCR Head (Cat. No. 50-152-7922)

Thermo Scientific™ KingFisher™ Flex Purification System with 96 KingFisher Head (Cat. No. 50-152-7923)

Thermo Scientific™ KingFisher™ Flex Purification System with 24 Deep-Well Head (Cat. No. 50-152-7925)

Thermo Scientific™ KingFisher™ Flex Purification System with 96 Deep-Well Head (Cat. No. 50-152-7924)



Thermo Scientific™ KingFisher™ Presto Purification System with 24 Deep-Well Head (Cat. No. 50-152-7931)

Thermo Scientific™ KingFisher™ Presto Purification System with 96 Deep-Well Head (Cat. No. 50-152-7930)



Thermo Scientific™ KingFisher™ Duo Prime Purification System (Cat. No. 14-387-700)

KingFisher instruments thermofisher.com/kingfisher

^{*} For laboratory use.

Plastics for KingFisher instruments



Apex

96 or 24 samples per run

Thermo Scientific™ Kingfisher™ 96 Combi Tip Comb, 100/Pack (Cat. No. 97-002-570)

Thermo Scientific[™] Kingfisher[™] 96 Deep-Well Plate, Barcoded, 50/Pack (Cat. No. 14-387-349)

Thermo Scientific[™] Kingfisher[™] 96 Deep-Well Plate, Sterile, Barcoded, 50/Pack (Cat. No. 14-387-350)

Thermo Scientific™ Kingfisher™ 96-Tip Comb for Deep-Well Magnet, Barcoded, 100/Pack (Cat. No. 14-387-354)

Thermo Scientific™ Kingfisher™ 96 Deep-Well Tip Comb and Plate, Sterile, Barcoded, 50/Pack (Cat. No. 14-387-358)

Thermo Scientific[™] Nunc[™] 96 Storage Tubes, 960/ Case (Cat. No. 12-570-208)

Thermo Scientific[™] Kingfisher[™] 96 PCR Tip Comb, 50/Pack (Cat. No. 97-002-560)

Thermo Scientific[™] Kingfisher[™] 96 Microplate (200 µL), Barcoded, 50/Pack (Cat. No. 14-387-355)

Thermo Scientific™ Kingfisher™ 96-Tip Comb, Barcoded, 100/Pack (Cat. No. 14-387-353)

Thermo Scientific™ Armadillo PCR Plate, 96 Deep-Well, Clear, Clear Wells, 25/Case (Cat. No. AB2396)

Thermo Scientific™ Armadillo PCR Plate, 96 Deep-Well, Semi-Skirted, Low Profile, Clear Wells, 25/Case (Cat. No. AB2496)

Thermo Scientific[™] Kingfisher[™] 24 Combi Tip Comb, 50/Pack (Cat. No. 97-002-580)

Thermo Scientific™ Kingfisher™ 24 Deep-Well Plate, Barcoded, 50/Pack (Cat. No. 14-387-351)

Thermo Scientific™ Kingfisher™ 24 Deep-Well Plate, Sterile, Barcoded, 50/Pack (Cat. No. 14-387-352)

Thermo Scientific™ Kingfisher™ 24 Deep-Well Tip Comb and Plate, Barcoded, 50/Pack (Cat. No. 14-387-356)

Thermo Scientific™ Kingfisher™ 24 Deep-Well Tip Comb and Plate, Sterile, Barcoded, 50/Pack (Cat. No. 14-387-357)





Flex

96 or 24 samples per run

Thermo Scientific[™] Kingfisher[™] 96-Tip Comb, 100/ Pack (Cat. No. 22-387-028)

Thermo Scientific[™] Kingfisher[™] 96-Tip Comb (For PCR Magnets), 80/Pack (Cat. No. 22-387-027)

Thermo Scientific[™] Kingfisher[™] 96 Deep-Well Plate, 50/Pack (Cat. No. 22-387-031)

Thermo Scientific[™] Kingfisher[™] 96 Deep-Well Plate, Sterile, 50/Pack (Cat. No. 22-387-032)

Thermo Scientific[™] Kingfisher[™] 24 Deep-Well Plate, 50/Pack (Cat. No. 22-387-034)

Thermo Scientific[™] Kingfisher[™] 24 Deep-Well Plate, Sterile, 50/Pack (Cat. No. 22-387-035)

Thermo Scientific[™] Kingfisher[™] 96 Microplate ((200 µL)), 48/Pack (Cat. No. 22-387-030)

Thermo Scientific[™] Pcr Plate, 96-Well, Skirted 50/Pack (Cat. No. AB-1300)

Thermo Scientific™ Nunc™ 96-Well Cap Mat, 50/Pack (Cat. No. 14-387-93)

Thermo Scientific[™] Nunc[™] 96-Well Cap Mat, Sterile, 25/Pack (Cat. No. 14-387-94)

Thermo Scientific[™] Kingfisher[™] Deep-Well 96-Tip Comb, 100/Pack (Cat. No. 22-387-029)

Thermo Scientific[™] Kingfisher[™] Deep-Well 96-Tip Comb and Plate, Sterile, 50/Pack (Cat. No. FER97002820)

Thermo Scientific[™] Kingfisher[™] Deep-Well 24-Tip Comb and Plate, 50/Pack (Cat. No. 22-387-033)

Thermo Scientific[™] Kingfisher[™] Deep-Well 24-Tip Comb and Plate, Sterile, 50/Pack (Cat. No. 14-387-739)

Plastics for KingFisher instruments



Presto

Thermo Scientific[™] Kingfisher[™] 96 Deep-Well Plate, 50/Pack (Cat. No. 22-387-031)

Thermo Scientific™ Kingfisher™ 96 Deep-Well Plate, Sterile, 50/Pack (Cat. No. 22-387-032)

Thermo Scientific™ Kingfisher™ 24 Deep-Well Plate, 50/Pack (Cat. No. 22-387-034)

Thermo Scientific™ Kingfisher™ 24 Deep-Well Plate, Sterile, 50/Pack (Cat. No. 22-387-035)

Thermo Scientific™ Kingfisher™ 96 Microplate (200 MI), 48/Pack (Cat. No. 22-387-030)

Thermo Scientific™ Superplate™ PCR Plate, 96-Well, Skirted, 25/Pack (Cat. No. Ab2800)

96 or 24 samples per run

Thermo Scientific[™] Kingfisher[™] Deep-Well 96-Tip Comb, 100/Pack (Cat. No. 22-387-029)

Thermo Scientific™ Kingfisher™ Deep-Well 96-Tip Comb and Plate, Sterile, 50/Pack (Cat. No. FER97002820)

Thermo Scientific™ Kingfisher™ Deep-Well 24-Tip Comb and Plate, 50/Pack (Cat. No. 22-387-033)

Thermo Scientific™ Kingfisher™ Deep-Well 24-Tip Comb and Plate, Sterile, 50/Pack (Cat. No. 14-387-739)



Duo Prime

6 or 12 samples per run

Thermo Scientific™ Kingfisher™ 96 Deep-Well Plate, 50/Pack (Cat. No. 22-387-031)

Thermo Scientific™ Kingfisher™ 96 Deep-Well Plate, Sterile, 50/Pack (Cat. No. 22-387-032)

Thermo Scientific™ Kingfisher™ 24 Deep-Well Plate, 50/Pack (Cat. No. 22-387-034)

Thermo Scientific™ Kingfisher™ 24 Deep-Well Plate, Sterile, 50/Pack (Cat. No. 22-387-035)

Thermo Scientific™ Kingfisher™ Duo 12-Tip Comb, 50/Pack (Cat. No. 14-387-291)

Thermo Scientific™ Kingfisher™ Duo Prime 6-Tip Comb, 48/Pack, and 24 Deep-Well Plate, 12/Pack (Cat. No. 14-387-292)

Thermo Scientific™ Kingfisher™ Duo Elution Strip For 12-Tip Format, 40/Pack (Cat. No. 14-387-293)

Thermo Scientific™ Kingfisher™ Duo Cap For Elution Strip, 40/Pack (Cat. No. 14-387-737)

Thermo Scientific™ Kingfisher™ Duo Combi Pack (Tips, Combs, Plates, and Elution Strips For 96 Samples, For 12-Tip Format) (Cat. No. 14-387-294)

KingFisher instruments thermofisher.com/kingfisher

Distributed by Fisher Scientific. Contact us today:

In the United States

Order online: fishersci.com Call customer service: 1-800-766-7000 In Canada

Order online: fishersci.ca

Call customer service: 1-800-234-7437

