

Hold a piece of your current tubing on top of the sizing chart to determine the best size for your needs. This guide includes many of the most popular tubing sizes. For those tubing sizes not listed here, a "Tubing Sizer" guide is available for download at www.fishersci.com

I.D.	1/32" (0.8mm)	1/16" (1.6mm)	3/32" (2.4mm)	1/8" (3.2mm)	1/8" (3.2mm)	1/8" (3.2mm)	1/8" (3.2mm)	5/32" (4mm)	5/32" (4mm)	3/16" (4.8mm)	3/16" (4.8mm)	3/16" (4.8mm)	3/16" (4.8mm)	3/16" (4.8mm)	3/16" (4.8mm)
O.D.	3/32 (2.4)	1/8 (3.2)	5/32 (4)	3/16 (4.8)	1/4 (6.4)	5/16 (7.9)	3/8 (9.5)	1/4 (6.4)	9/32 (7.1)	1/4 (6.4)	9/32 (7.1)	5/16 (7.9)	3/8 (9.5)	9/16 (14)	7/16 (11)
Wall	1/32 (0.8)	1/32 (0.8)	1/32 (0.8)	1/32 (0.8)	1/16 (1.6)	3/32 (2.4)	1/8 (3.2)	3/64 (1.2)	1/16 (1.6)	1/32 (0.8)	9/64 (1.2)	1/16 (1.6)	3/32 (2.4)	3/16 (4.8)	1/8 (3.2)

I.D.	1/4" (6.4mm)	1/4" (6.4mm)	1/4" (6.4mm)	1/4" (6.4mm)	1/4" (6.4mm)	5/16" (7.9mm)	5/16" (7.9mm)	5/16" (7.9mm)	5/16" (7.9mm)	3/8" (9.5mm)	3/8" (9.5mm)	3/8" (9.5mm)
O.D.	3/8 (9.5)	7/16 (11)	1/2 (12.7)	5/8 (15.8)	1 (25.4)	7/16 (11)	1/2 (12.7)	9/16 (14)	11/16 (17.4)	1/2 (12.7)	9/16 (14)	5/8 (15.8)
Wall	1/16 (1.6)	3/32 (2.4)	1/8 (3.2)	3/16 (4.8)	3/8 (9.5)	1/16 (1.6)	3/32 (2.4)	1/8 (3.2)	3/16 (4.8)	1/16 (1.6)	3/32 (2.4)	1/8 (3.2)

I.D.	3/8" (9.5mm)	3/8" (9.5mm)	3/8" (9.5mm)	7/16" (11mm)	1/2" (12.7mm)	1/2" (12.7mm)	1/2" (12.7mm)	1/2" (12.7mm)
O.D.	7/8 (22)	1 (25.4)	1 1/8 (29)	9/16 (14)	5/8 (15.8)	11/16 (17.4)	3/4 (19)	1 (25.4)
Wall	1/4 (6.4)	3/16 (7.9)	3/8 (9.5)	1/16 (1.6)	1/16 (1.6)	3/32 (2.4)	1/8 (3.2)	1/4 (6.4)