

GILSON PIPETTE SELECTION GUIDE

	DESCRIPTION	THROUGHPUT	COMFORT	MODEL / VOLUME	BENEFITS
SINGLE CHANNEL, AIR DISPLACEMENT	PIPETMAN® M PIPETMAN® M Connected	L — M — H Medium to High		8 single channel models Volume Range: 0.5 - 10 mL	 Ease-of-use On-target performance PIPETMAN® M Connected makes manual processes verifiable
	PIPETMAN* L	L — M — H Low to Medium		8 single channel models Volume Range: 0.2 - 10 mL Fixed Volume: 1 - 5000 μL	 All day pipetting comfort Secure pipetting Fully autoclavable
	PIPETMAN* G	L — M — H Low to Medium		8 single channel models Volume Range: 0.2 - 10 mL	Pipetting comfortReliable resultsBuilt-to-last and convenient
	PIPETMAN* Classic	L — M — H Low		8 single channel models Volume Range: 0.2 - 10 mL	Built-to-last Extremely easy to maintain
MULTICHANNEL	PIPETMAN* M PIPETMAN* M Connected	L — M — H Medium to High		12 multichannel models Volume Range: 0.5 - 1200 μL	 Ease-of-use On-target performance PIPETMAN® M Connected makes manual processes verifiable
	PIPETMAN® L	L — M — H Medium to High		8 multichannel models Volume Range: 0.5 - 300 μL	 All day pipetting comfort Secure pipetting Fully autoclavable
	PIPETMAN® G	L — M — H Medium to High		8 multichannel models Volume Range: 1 - 300 μL	Pipetting comfortReliable resultsBuilt-to-last and convenient
SPECIALTY	MICROMAN® E	L — M — H Low		6 single channel models Volume Range: 1 - 1000 μL	 Reliable results even with non-aqueous liquids Overall protection Designed with comfort in mind
SEMI-AUTO	PLATEMASTER*	L — M — H High		96- or 384-well plates Volume Range: 0.5 - 220 μL	Save time and increase your productivitySimplify sample prepConvenient for any microplate application
AUTOMATED	PIPETMAX*	L — M — H High		3 pipette head options 8 channel 1 - 20 μL 8 channel 20 - 200 μL 4 channel 50 - 1200 μL	 Upgrade to automation for reliable, accurate pipetting Free yourself from tedious sample prep work Stay flexible for now and for the future PIPETMAN® inside

Contact us today:

In the United States

Order online: fishersci.com
Fax an order: 1-800-926-1166
Call customer service: 1-800-766-7000

