



Chemicals

2024 Supplier Guide

 **fisher scientific**
part of Thermo Fisher Scientific

Cambridge Isotopic Laboratories** +

- NMR Solvents

Decon™ Labs, Inc.

- Detergents/Cleaners
- Disinfectants
- Non-Sterile Alcohol
- Pure Ethanol
- Skincare
- Sterile, USP Purified Water
- Sterile, WFI Water

Fisher Bioreagents

- Buffers
- Cell Culture Reagents and Additives
- Core Bioreagents
- High-Purity Water
- Nucleic Acid Purification
- PCR
- Solutions
- Solvents
- Western Blotting

Fisher Chemical

- Acids and Bases
- Aqualine™ Karl Fischer Titration Reagents
- Buffers and Inorganic Salts
- GC Headspace Solvents
- GC Resolv™ Solvents
- Optima™ LC/MS Solvents
- Optima™ LC Solvents
- Optima™ and TraceMetal™ Acids
- Solutions
- Solvents

Honeywell™ Research Chemicals

- Burdick & Jackson™ Solvents
- Chromasolv™ Solvents
- Fluka™ Analytical Reagents
- Hydranal™ Karl Fischer Titration Reagents
- Riedel-de Haën™ Solvents
- TraceSELECT™ Acids and Inorganics

Cytiva Hyclone

- cGMP Water
- Molecular Ultra-Pure Water
- Multi-Compendial Custom Solutions
- Water, Purified, USP
- Water for Injection, USP/EP
- Water for Irrigation, USP

Invitrogen**

- Core Bioreagents

J.T.Baker

- Acids and Bases
- Gas Chromatography Products
- HPLC Products
- Inorganic Salts
- LC/MS Products
- ULTRA LC/MS™ Products

LabChem

- Acids and Bases
- Buffers
- Custom Capabilities
- Solutions
- Solvents
- Standards

Macron Fine Chemicals

- Acids
- ACS Reagent Chemicals and Solvents
- Gas Chromatography Solvents
- HPLC Solvents and Reagents

MP Biomedicals

- Amino Acids
- Antibiotics
- Animal Research Feed
- Biomacromolecules
- Buffers
- Carbohydrates
- Core Bioreagents
- Media Capsules
- Salts
- Scintillation Cocktails
- Surfactants

Regent Chemical*

- Acids

RICCA Chemical Company

- Acids, Bases, Salts
- Buffers
- Custom Capabilities
- High-Purity Water
- Microbiology Stains and Reagents
- Solutions
- Solvents
- Standards

Spectrum™ Chemical

- Active Pharmaceutical Ingredients
- Biocertified Chemicals
- BP/EP/JP Grades
- cGMP Chemicals
- Excipients
- Food Additives and Preservatives
- Kosher/Halal Grades
- USP/NF/FCC Grades
- USP Test Solutions
- Vitamins

Spex CertiPrep

- Buffers
- Custom Capabilities
- Inorganic Certified Reference Materials (ISO Guide 34)
- Organic Certified Reference Materials (ISO Guide 34)

Supelco™ from MilliporeSigma

- Acids, Bases, and Salts
- Aquastar™ Karl Fischer Reagents
- Dry and Deuterated Solvents
- EMSURE™ Solvents and Inorganics
- HPLC, LC-MS, GC, and Spectroscopy Solvents
- Standards and Certified Reference Materials
- Testing Kits and Strips

TCI America

- Bioorganic Chemicals
- Organic Building Blocks
- Organometallic Complexes

Thermo Scientific

- AcroSeal™ Anhydrous Solvents
- Bioorganic Chemicals
- Catalysts
- Core Bioreagents
- Deuterated Solvents (NMR)
- Drug Discovery Screening Libraries
- Gibco™ Processing Liquids
- High-Purity Solvents
- High-Purity Water
- ICP-OES Acids
- Inorganic Salts
- Organic Building Blocks
- Organic Photovoltaics
- Organometallic Complexes
- Organometallic Reagents in Solution
- Production Chemicals and Services
- Puratonic and Reaction High-Purity Inorganics
- Synthesis Reagents

*Canada Only

**Encompass

*U.S. Only

Blue denotes supplier supported by the chemical specialist team.

Distributed by Fisher Scientific. Contact us today:

In the United States

Order online: fishersci.com

Call customer service: 1-800-766-7000

In Canada

Order online: fishersci.ca

Call customer service: 1-800-234-7437

