## HandPRO

# 9100 / 9300 SERIES



#### CLEANROOM NITRILE GLOVES

ISO 5 / ISO 4 COMPATIBLE | 12" (300 mm) Length

# PROTECT YOUR PEOPLE AND YOUR PRODUCTS

HandPRO® 9100 Nitrile Clean Class 100 Gloves and HandPRO® 9300 Nitrile Ultra Clean Class 10 Gloves are made from patented accelerator-free LOW DERMA™ nitrile technology.\* The consistently low endotoxin levels, comfort and performance of these 12" sulfur-free gloves make them a top choice for people and product protection.



### PRODUCT SPECIFICATIONS

- Not Made with Natural Rubber Latex
- Powder-Free
- Sulfur-Free
- Accelerator-Free
- · Low Endotoxin Levels
- Ambidextrous
- · Low Dye White Color
- · Anti-Fatigue Compound
- Anti-Slip Grip
- Finger-Textured

Manufactured under ISO 13485, CAN/CSA ISO 13485, ISO 9001 and US FDA QSR Quality Management System
IEST-RP-CC005 Recommended Practice for Cleanroom Gloves

#### **GLOVE THICKNESS**

Typical Values (mm/mils)

Cuff 0.08 - 0.09 | 3.1 - 3.5 Palm 0.10 - 0.11 | 3.9 - 4.3 Fingertip 0.14 - 0.16 | 5.5 - 6.2

#### GLOVE LENGTH

Typical Values (mm)

303 - 305 (12")

#### **AQL**

Watertight Test 2.5

#### PHYSICAL PROPERTIES (Before Aging)

Tensile Strength 23.8 - 28 MPa Elongation 560 - 580%

"Your Protection Is Our Purpose" Hourglass-Intl.com

\*Patent www.LowDerma.com/patents

# PACKAGING

100/Bag; 1000/Case Double-Bagged



**LOW DERMA™** Accelerator-Free Gloves reduce your risk of developing Type IV chemical allergies caused by sufur-based accelerators. NO thiurams, carbamates or mercaptobenzothiazoles (MBTs.)



Consistently Low Endotoxin Levels in a non-sterile glove with low bio-burden levels



Advanced Cross-Linking Nitrile Compound for a stronger glove with enhanced tactile sense and reduced hand fatigue

Size	Mfr. No.	Cat. No.	Mfr. No.	Cat. No.
XS	9100	19-423-100	9300	17-900-900
S	9101	19-423-101	9301	17-900-901
М	9102	19-423-102	9302	17-900-902
L	9103	19-423-103	9303	17-900-903
XL	9104	19-423-104	9304	17-900-904
XXL	9105	19-423-105	9305	17-900-905

Distributed by Fisher Scientific. Contact us today:

In the United States

Order online: fishersci.com Call customer service: 1-800-766-7000 In Canada

Order online: fishersci.ca Call customer service: 1-800-234-7437

