



## Test Menu

# Atellica Solution

For use  
in the  
U.S.



Flexible, scalable, automation-ready immunoassay and clinical chemistry analyzers engineered to deliver control and simplicity so you can drive better outcomes.

Experience the power of the Atellica® Solution, featuring patented bidirectional magnetic sample transport technology, the flexibility to create over 300 customizable configurations, and a broad assay menu with proven detection technologies.



### Chemistry

#### Diabetes

Fructosamine  
Hemoglobin A1c (Enzymatic)

#### Drugs of Abuse/Toxicology

6-Acetylmorphine (6-AM)\*  
Acetaminophen  
Amphetamines  
Barbiturates, Urine  
Barbiturates, Serum\*  
Benzodiazepines, Urine  
Benzodiazepines, Serum\*  
Buprenorphine\*  
Cannabinoids (THC)  
Cocaine Metabolite  
Ecstasy  
Ethyl Alcohol  
Fentanyl†  
Lysergic Acid Diethylamide (LSD)\*  
Methadone  
Methadone Metabolite (EDDP)†  
Methaqualone\*  
Opiates  
Oxycodone  
Phencyclidine  
Propoxyphene  
Salicylate  
Tramadol†  
Tricyclic Antidepressants\*

#### General Chemistry

Alanine Aminotransferase (ALT)  
Alanine Aminotransferase (P5P)  
Albumin (BCG)  
Albumin (BCP)  
Alkaline Phosphatase  
Ammonia  
Amylase  
Angiotensin-converting enzyme (ACE)†  
Aspartate Aminotransferase (AST)  
Aspartate Aminotransferase (P5P)  
Bilirubin, Direct  
Bilirubin, Total  
Calcium (Arsenazo)  
Calcium (CPC)  
Carbon Dioxide  
Chloride  
Cholesterol  
Cholinesterase  
Creatine Kinase  
Creatinine  
Creatinine (Enzymatic)  
Gamma-Glutamyl Transferase (GGT)  
Glucose (Hexokinase)  
Glucose (Oxidase)  
HDL Cholesterol  
Iron  
Lactate  
Lactate, CSF  
Lactate Dehydrogenase (L-P)  
LDL Cholesterol

Lipase  
Magnesium  
Microalbumin  
Phosphorus  
Potassium  
Sodium  
Total Iron Binding Capacity (TIBC)  
Total Protein  
Total Protein, Urine/CSF  
Triglycerides  
Urea Nitrogen (BUN)  
Uric Acid

#### Immunosuppressant Drugs

Tacrolimus

#### Specific Proteins

α1-Acid Glycoprotein (AAG)  
α1-Antitrypsin (AAT)  
Antistreptolysin O (ASO)  
Apolipoprotein A-1  
Apolipoprotein B  
β-2 Microglobulin  
Ceruloplasmin†  
Complement C3  
Complement C4  
CRP  
CRP, High Sensitivity  
Cystatin C  
Free Light Chain kappa\*  
Free Light Chain lambda\*  
Haptoglobin  
Immunoglobulin A (IgA)  
Immunoglobulin G (IgG)  
Immunoglobulin M (IgM)

Lipoprotein(a)  
Prealbumin  
Rheumatoid Factor (RF)  
Transferrin

#### Specimen Validity Testing

Creatinine\*  
Nitrite\*  
Oxidant\*  
pH\*  
Specific Gravity\*

#### Therapeutic Drug Monitoring

Amikacin\*  
Caffeine\*  
Carbamazepine  
Digoxin  
Gabapentin††  
Gentamicin  
Lamotrigine†  
Levetiracetam†  
Lidocaine  
Lithium  
Methotrexate†  
N-Acetylprocainamide (NAPA)  
Phenobarbital  
Phenytoin  
Procainamide  
Theophylline  
Tobramycin  
Valproic Acid  
Vancomycin  
Voriconazole††

\*Alliance application manufactured and distributed by Siemens Healthcare Diagnostics Inc.

†Alliance application manufactured by third party, distributed by Siemens Healthcare Diagnostics Inc.

‡Under development. Not commercially available. Future availability cannot be guaranteed.

Find it at [fisherhealthcare.com](http://fisherhealthcare.com)

# Atellica Portfolio of Laboratory Products

Engineered by Siemens Healthineers to deliver control and simplicity so you can drive better outcomes.

Tighter control of your lab, simplified workflow, and more time to focus on driving better business and clinical outcomes—that's the promise of our Atellica® portfolio of laboratory products.

# Control. Simplicity. Better Outcomes.

For use  
in the  
U.S.

## Atellica Solution Test Menu



### Immunoassay

#### Anemia

Active-B12  
EPO  
Ferritin  
Folate  
RBC Folate  
Vitamin B12

#### Autoimmune

Anti-CCP IgG

#### Bone Metabolism

Intact PTH  
Vitamin D Total

#### Cardiac

BNP  
CKMB  
High-Sensitivity Troponin I  
Myoglobin  
NT-proBNP II†

#### Diabetes

C-Peptide  
Insulin

#### Growth

Growth Hormone (hGH)†  
IGF-I†  
IGFBP-3†

#### Hepatitis

Anti-HBe†  
Anti-HBs 2  
HAV IgM  
HAV Total  
HBc IgM  
HBc Total  
HBeAg  
HBsAg II  
HBsAg Confirmatory  
HCV

#### HIV

HIV 1/O/2 Enhanced (EHIV)  
HIV Ag/Ab Combo (CHIV)

#### Immunosuppressant Drugs

Cyclosporine  
Everolimus†  
Sirolimus†  
Tacrolimus†

#### Inflammation

IgE, Total  
IL2R†  
TNFα†

#### Liver Disease

Enhanced Liver Fibrosis  
(ELF™) Test

#### Metabolic

ACTH†  
Cortisol  
Homocysteine

#### Neurology

β-Amyloid 1-42 (AB42)†  
Serum Neurofilament light  
chain (sNFL)†  
Total-Tau (TTAU)†

#### Oncology

AFP  
BR 27.29  
CA 125II™  
CA 15-3™  
CA 19-9™  
Calcitonin  
CEA  
Complexed PSA  
CYFRA 21-1†  
Free PSA II†  
PSA  
Serum HER-2/neu

#### Reproductive Endocrinology

Androstenedione  
Anti-Mullerian Hormone  
(AMH)\*\*  
DHEA-SO4  
Enhanced Estradiol  
FSH  
hCG  
LH  
PIGF†  
Progesterone  
Prolactin  
sFlt-1†  
SHBG  
Testosterone II

#### Research Use Only

Free β-hCG  
HBsAg II Quant  
IL-6  
PAPP-A

#### Sepsis

Procalcitonin (PCT)

#### Special ID

EBV-EBNA IgG†  
EBV-VCA IgG†  
EBV-VCA IgM†  
SARS-CoV-2 Ag (CoVAg)\*\*  
SARS-CoV-2 IgG (sCOVG)††  
SARS-CoV-2 Total (COV2T)††  
Syphilis  
Zika Test

#### Therapeutic Drug Monitoring

Digitoxin  
Digoxin

#### Thyroid

Anti-TG  
Anti-TPO  
Free T3  
Free T4  
Thyroglobulin (Tg)†  
Total T3  
Total T4  
TSH3-Ultra  
T Uptake

#### TORCH

CMV IgG  
CMV IgM†  
Herpes-1 IgG  
Herpes-2 IgG  
Rubella IgG  
Rubella IgM  
Toxoplasma IgG  
Toxoplasma IgM

†Under development. Not commercially available. Future availability cannot be guaranteed.

§CA 125II, CA 15-3, and CA 19-9 are trademarks of Fujirebio Diagnostics, Inc.

\*\*Under FDA review. Not available for sale in the U.S.

††This test has not been FDA cleared or approved. This test has been authorized by FDA under an EUA for use by authorized laboratories. This test has been authorized only for detecting the presence of antibodies against SARS-CoV-2, not for any other viruses or pathogens. This test is only authorized for the duration of the declaration that circumstances exist justifying the authorization of emergency use of in vitro diagnostics for detection and/or diagnosis of COVID-19 under Section 564(b)(1) of the Act, 21 U.S.C. § 360bbb-3(b)(1), unless the authorization is terminated or revoked sooner. Product availability may vary by country and is subject to varying regulatory requirements.

Atellica, ELF, and all associated marks are trademarks of Siemens Healthcare Diagnostics Inc., or its affiliates. All other trademarks and brands are the property of their respective owners.

Product availability may vary from country to country and is subject to varying regulatory requirements.

## Contact your Fisher Healthcare representative to learn more.

Distributed by Fisher Healthcare. Contact us today:

In the United States

Order online: [fisherhealthcare.com](http://fisherhealthcare.com)

Call customer service: 1-800-640-0640



© 2023 Thermo Fisher Scientific Inc. All rights reserved.

Trademarks used are owned as indicated at [fishersci.com/trademarks](http://fishersci.com/trademarks).

BN235868254-US



[siemens-healthineers.com](http://siemens-healthineers.com)

Published by Siemens Healthcare Diagnostics Inc.

Laboratory Diagnostics

Tarrytown, NY 10591-5005 USA