



WHEATON®

CRIMP/SERUM VIALS



DWK Life Sciences is the manufacturer of high-quality medical grade glass vials formed from the highest quality pharmaceutical-grade tubing, conforming to USP <660> / EP3.2.1 / JP <7.01> standards for injectable packaging and the safe storage and delivery of drug content. Vials are designed for the short- and long-term storage of parenteral, lyophilized, reagent, and vaccine content.

Product Highlights

- | | |
|---|--|
| <ul style="list-style-type: none">• Clear and amber, Type I, tubular, low-expansion, borosilicate glass conforms to ASTM and USP requirements | <ul style="list-style-type: none">• Global ISO 15378 certified manufacturing |
| <ul style="list-style-type: none">• ISO 8362-1, GPI 2710, and Custom design | <ul style="list-style-type: none">• Certified pre-sterilized Ready-to-Use configurations |
| <ul style="list-style-type: none">• European, American, and no blowback* | <ul style="list-style-type: none">• CCI validated stoppers, seals, and snap caps |
| <ul style="list-style-type: none">• Small minimum order requirements | <ul style="list-style-type: none">• Autoclavable |

*No blowback is only available in a custom made vial

DWK Life Sciences SALES PARTNER

GPI 2710 EP US Blowback Serum Vial Configurations

Catalog Pack
Shrink Wrapped Tray

Carton Bulk Pack
Shrink-wrapped Trays in Case Packs

Unitized Pallet
Shrink-wrapped Trays on Unitized Pallets

Fisher Scientific Standard Pack Cat. No.	Size (mL)	Brimful Capacity (mL)	Catalog Pack Qty	Fisher Scientific Bulk Pack Cat. No.	Carton	Case Qty	Fisher Scientific Pallet Cat. No.	Vials/ Unitized Pallet
Clear								
01-671-211	2	3.2	225	01-257-617	12	2,700	01-257-616	68,400
01-671-205	3	4.8	169	01-257-613	10	1,690	01-257-612	51,376
01-671-208	5	10	100	01-257-609	10	1,000	01-257-608	30,400
01-671-209	10	15.2	150	01-257-621	14	2,100	01-257-620	39,600
Amber								
01-671-210	2	3.2	225	01-257-619	12	2,700	01-257-618	68,400
01-671-204	3	4.8	169	01-257-615	10	1,690	01-257-614	51,376
01-671-206	5	10	100	01-257-611	10	1,000	01-257-610	30,400
01-671-207	10	15.2	150	01-257-623	14	2,100	01-257-622	39,600

GPI 2710 EP US Blowback Serum Vial Dimensions

Fisher Scientific Cat. No.	OD (mm)	Height (mm)	Wall (mm)	Finish (mm)	Tray Size (inches)	Carton	Carton Size (inches)	Pallet
2 mL Clear								
01-257-616	14.75	32	1.00	13	9.125 x 7.75 x 1.25	—	—	Plastic
01-257-617	14.75	32	1.00	13	9.125 x 7.75 x 1.25	12	16.125 x 9.875 x 8.5625	—
01-671-211	14.75	32	1.00	13	9.125 x 7.75 x 1.25	1	9.875 x 8.125 x 2.125	—
2 mL Amber								
01-257-618	14.75	32	1.00	13	9.125 x 7.75 x 1.25	—	—	Plastic
01-257-619	14.75	32	1.00	13	9.125 x 7.75 x 1.25	12	16.125 x 9.875 x 8.5625	—
01-671-210	14.75	32	1.00	13	9.125 x 7.75 x 1.25	1	9.875 x 8.125 x 2.125	—
3 mL Clear								
01-257-612	16.75	37.7	1.10	13	9.125 x 7.75 x 1.25	—	—	Plastic
01-257-613	16.75	37.7	1.10	13	9.125 x 7.75 x 1.25	10	16.125 x 9.875 x 8.5625	—
01-671-205	16.75	37.7	1.10	13	9.125 x 7.75 x 1.25	1	9.875 x 8.125 x 2.125	—
3 mL Amber								
01-257-614	16.75	37.7	1.10	13	9.125 x 7.75 x 1.25	—	—	Plastic
01-257-615	16.75	37.7	1.10	13	9.125 x 7.75 x 1.25	10	16.125 x 9.875 x 8.5625	—
01-671-204	16.75	37.7	1.10	13	9.125 x 7.75 x 1.25	1	9.875 x 8.125 x 2.125	—
5 mL Clear								
01-257-608	21.75	40	1.20	20	9.125 x 7.75 x 1.25	—	—	Plastic
01-257-609	21.75	40	1.20	20	9.125 x 7.75 x 1.25	10	16.125 x 9.875 x 8.5625	—
01-671-208	21.75	40	1.20	20	9.125 x 7.75 x 1.25	1	9.875 x 8.125 x 2.125	—
5 mL Amber								
01-257-610	21.75	40	1.20	20	9.125 x 7.75 x 1.25	—	—	Plastic
01-257-611	21.75	40	1.20	20	9.125 x 7.75 x 1.25	10	16.125 x 9.875 x 8.5625	—
01-671-206	21.75	40	1.20	20	9.125 x 7.75 x 1.25	1	9.875 x 8.125 x 2.125	—
10 mL Clear								
01-257-620	23.75	50	1.30	20	12.5 x 10.5 x 1.75	—	—	Plastic
01-257-621	23.75	50	1.30	20	12.5 x 10.5 x 1.75	14	21.625 x 13.25 x 15.0625	—
01-671-209	23.75	50	1.30	20	12.5 x 10.5 x 1.75	1	13.25 x 10.875 x 3.3125	—
10 mL Amber								
01-257-622	23.75	50	1.30	20	12.5 x 10.5 x 1.75	—	—	Plastic
01-257-623	23.75	50	1.30	20	12.5 x 10.5 x 1.75	14	21.625 x 13.25 x 15.0625	—
01-671-207	23.75	50	1.30	20	12.5 x 10.5 x 1.75	1	13.25 x 10.875 x 3.3125	—

ISO 8362-1 EP European Blowback Serum Vial

Catalog Pack
Shrink Wrapped Tray

Carton Bulk Pack
Shrink-wrapped Trays in Case Packs

Unitized Pallet
Shrink-wrapped Trays on Unitized Pallets

Fisher Scientific Standard Pack Cat. No.	Size (mL)	Brimful Capacity (mL)	Catalog Pack Qty	Fisher Scientific Bulk Pack Cat. No.	Carton	Case Qty	Fisher Scientific Pallet Cat. No.	Vials/Unitized Pallet
Clear								
01-670-187	2	4	196	01-257-629	12	2,352	01-257-628	59,584
01-670-188	6	10	100	01-257-627	10	1,000	01-257-626	30,400
01-670-189	10	13.5	150	01-257-625	16	2,400	01-257-624	43,200

ISO 8362-1 EP European Blowback Serum Vial

Fisher Scientific Cat. No.	OD (mm)	Height (mm)	Wall (mm)	Finish (mm)	Tray Size (inches)	Carton	Carton Size (inches)	Pallet
2R Clear Vial								
01-257-628	16	35	1.00	13	9.125 x 7.75 x 1.25	—	—	Plastic
01-257-629	16	35	1.00	13	9.125 x 7.75 x 1.25	12	16.125 x 9.875 x 8.5625	—
01-670-187	16	35	1.00	13	9.125 x 7.75 x 1.25	1	—	—
6R Clear Vial								
01-257-626	22	40	1.00	20	9.125 x 7.75 x 1.25	—	—	Plastic
01-257-627	22	40	1.00	20	9.125 x 7.75 x 1.25	10	16.125 x 9.875 x 8.5625	—
01-670-188	22	40	1.00	20	9.125 x 7.75 x 1.25	1	—	—
10R Clear Vial								
01-257-624	24	45	1.00	20	12.5 x 10.5 x 1.75	—	—	Plastic
01-257-625	24	45	1.00	20	12.5 x 10.5 x 1.75	16	21.625 x 13.25 x 15.0625	—
01-670-189	24	45	1.00	20	12.5 x 10.5 x 1.75	1	—	—





Excellence in your hands

038 / WTD 11-2023

Contact us at [DWK.com](https://www.dwk.com)

© 2024 DWK Life Sciences • The trademarks used are owned by DWK Life Sciences GmbH, DWK Life Sciences LLC or DWK Life Sciences Ltd.

DWK Life Sciences SALES PARTNER

Distributed by Fisher Scientific. Contact us today:

In the United States

Order online: fishersci.com

Call customer service: 1-800-766-7000

In Canada

Order online: fishersci.ca

Call customer service: 1-800-234-7437

 **fisher scientific**
part of **Thermo Fisher Scientific**

© 2024 Thermo Fisher Scientific Inc. All rights reserved.

Trademarks used are owned as indicated at fishersci.com/trademarks.

01/24 BN247719958-NA