

Our engineers have been designing and manufacturing high-quality thermal cyclers since 1987. In that time, Applied Biosystems[™] thermal cyclers have built a reputation for reliability, accuracy, and user-friendly interfaces. Our instruments enable precise, consistent results for every challenge, application, and budget.

Key features	Ultimate flexibility and throughput	Ultimate performance	Elegantly simple and precise	Precise PCR	Routine PCR	Designed for easy robotic integration
	ProFlex™ PCR System	VeritiPro [™] Thermal Cycler	SimpliAmp [™] Thermal Cycler	MiniAmp™ Plus Thermal Cycler	MiniAmp [™] Thermal Cycler	Automated Thermal Cycler
						Normal Parameter Normal Parameter Little Little Little Little And Andrews
Max. sample throughput	480,000 reactions	384 reactions	96 reactions	96 reactions	96 reactions	384 reactions
Max. block ramp rate	6.0°C/sec	6.0°C/sec	4.0°C/sec	3.5°C/sec	3.0°C/sec	3.5°C/sec
Block formats (temperature optimization)	3 x 32-well 0.2 mL (2-zone VeriFlex™ Block) 96-well 0.2 mL (6-zone VeriFlex Block) 2 x 96-well 0.2 mL 2 x flat block 2 x 384-well 0.02 mL	96-well 0.2 mL (6-zone VeriFlex Block) 384-well (isothermal block)	96-well 0.2 mL (3-zone VeriFlex Block)	96-well 0.2 mL (3-zone VeriFlex Block)	• 96-well 0.2 mL	96-well 0.2 mL (compatible with full- or semi-skirted plates) 384-well 0.02 mL

Easily find compatible PCR plastics for your thermal cycler using our plastics selection tool. Find the perfect pairing at thermofisher.com/findplastics.

Don't forget reagents—choose from PCR enzymes you know and trust, such as Invitrogen™ SuperScript™ reverse transcriptases and Invitrogen™ Platinum™ SuperFi™ reagents. Discover more at **thermofisher.com/pcr**.



applied biosystems

Save up to 33%

on thermal cycler starter packages*

Starter packages have everything you need to get started with your new PCR system, including a thermal cycler and PCR plastics. Find a package to meet your needs today.

Ordering information

Description	Cat. No.
ProFlex PCR System + Plastics Package, 3 x 32-well, 8-tube strips	A41182
ProFlex PCR System + Plastics Package, 3 x 32-well, TriFlex plates	A41183
ProFlex PCR System + Plastics Package, 1 x 96-well, EnduraPlate plates	A41184
ProFlex PCR System + Plastics Package, 1 x 96-well, 8-tube strips	A41185
ProFlex PCR System + Plastics Package, 2 x 96-well, EnduraPlate plates	A41186
ProFlex PCR System + Plastics Package, 2 x 384-well, EnduraPlate plates	A41187
VeritiPro Thermal Cycler + Plastics Package, 96-well, 8-tube strips	A47396
VeritiPro Thermal Cycler + Plastics Package, 96-well, EnduraPlate plates	A47397
VeritiPro Thermal Cycler + Plastics Package, 96-well, TriFlex plates	A47398
VeritiPro Thermal Cycler + Plastics Package, 384-well, EnduraPlate plates	A47399
SimpliAmp Thermal Cycler + Plastics Package, 8-tube strips	A41192
SimpliAmp Thermal Cycler + Plastics Package, EnduraPlate plates	A41193
MiniAmp Thermal Cycler + Plastics Package, 8 tube strips	A41194
MiniAmp Thermal Cycler + Plastics Package, 3 x 32-well, TriFlex plates	A41195
MiniAmp Plus Thermal Cycler + Plastics Package, 8 tube strips	A41196
MiniAmp Plus Thermal Cycler + Plastics Package, 3 x 32-well, TriFlex plates	A41197
Automated Thermal Cycler (ATC) + Plastics Package, 96-well, half-skirt EnduraPlate plates	A41198
Automated Thermal Cycler (ATC) + Plastics Package, 96-well, full-skirt EnduraPlate plates	A41199

Note: Additional starter packages with warranty and service are also available. Contact your Fisher Scientific sales representative to learn more.

Visit **fishersci.com/thermalcyclerkits** or **fishersci.ca/thermalcyclerkits** to save up to 33% on thermal cycler starter packages.

*Offer valid January 1, 2023 to December 31, 2023. Savings based on the cost of purchasing the packaged products separately. Discounts taken off list price. Prices shown reflect promotional prices. U.S. customers acknowledge that this offer may include a discount or other price reduction that must be properly and accurately accounted for and reported by customer in accordance with all federal and state laws, including without limitation the federal anti-kickback law (42 U.S.C. § 1320a-7b(b)(3)(A)) and regulations thereunder (42 C.F.R. §1001.952(h)). Canada customers acknowledge that this offer may include a discount or other price reduction that must be properly and accurately accounted for and reported by customer as applicable.

Distributed by Fisher Scientific. Contact us today:

In the United States

Order online: fishersci.com

Call customer service: 1-800-766-7000

In Canada

Order online: fishersci.ca

Call customer service: 1-800-234-7437

