

Fisherbrand Sorbents and Spill Products

Choose Fisherbrand™ sorbents and spill kits to clean up universal, chemical, and oil-only spills in laboratory, healthcare, and industrial facilities.



In areas where chemicals are present, brightly colored Fisherbrand Chemical Pads alert users to exercise caution.



Fisherbrand single-ply Universal Pads are your general-purpose solution for small to medium leaks and spills.




Rely on Fisherbrand Single-Use Spill Kits, available in acid, caustic, flammable, and combination versions.

Fisherbrand Sorbents and Spill Products


Fisherbrand Absorbent Products

	Type	Dimensions	Capacity	Quantity	Cat. No.
	Pad, Lightweight, Gray	15 x 19 in.	44 gal. (165.5 L)	200/Case	19-140-910
	Pad, Medium Weight, Gray	15 x 19 in.	25 gal. (94.6 L)	100/Case	19-140-911
	Roll, Medium Weight, Gray	30 in. x 150 ft.	38 gal. (143.8 L)	Each	19-140-913
	Roll, Lightweight, Gray	30 in. x 300 ft.	42.5 gal. (160.8 L)	Each	19-140-914
	Pillow, Gray	18 x 18 in.	28 gal. (106 L)	16/Case	19-140-912
	SOC, Gray	3 x 42 in.	40.5 gal. (153.3 L)	20/Case	19-140-915

Absorbents for Oil Only

	Type	Dimensions	Capacity	Quantity	Cat. No.
	Pad, Lightweight, White	15 x 19 in.	44 gal. (165.5 L)	200/Case	19-140-910
	Pad, Medium Weight, White	15 x 19 in.	25 gal. (94.6 L)	100/Case	19-140-911
	Roll, Medium Weight, White	30 in. x 150 ft.	38 gal. (143.8 L)	Each	19-140-913
	Roll, Lightweight, White	30 in. x 300 ft.	42.5 gal. (160.8 L)	Each	19-140-914
	Pillow, White	18 x 18 in.	28 gal. (106 L)	16/Case	19-140-912
	SOC, White	3 x 42 in.	40.5 gal. (153.3 L)	20/Case	19-140-915
	Loose				

Fisherbrand Chemical Absorbent Products

	Type	Dimensions	Capacity	Quantity	Cat. No.
	Pad, Heavyweight, Yellow	15 x 19 in.	22 gal. (83.2 L)	100/Case	19-140-918
	Roll, Heavyweight, Yellow	30 in. x 150 ft.	40 gal. (151.4 L)	Each	19-140-919
	SOC, Green	3 in. x 4 ft.	12 gal. (45.4 L)	12/Pack	19-140-920

Fisherbrand Single-Use Spill Kits

	Type	Includes	Cat. No.
	Acid Neutralizing Spill Kit	3 lb. Granular Sorbent, 2 lb. Acid Neutralizing Powder, 1 Pair Goggles, 1 Pair Gloves, 1 Apron, 1 Dustpan, 1 Hand Broom, 1 Spatula, 2 Disposal Bags and Labels	19-140-935
	Base Neutralizing Spill Kit	3 lb. Granular Sorbent, 2 lb. Base Neutralizing Powder, 1 Pair Goggles, 1 Pair Gloves, 1 Apron, 1 Dustpan, 1 Hand Broom, 1 Spatula, 2 Disposal Bags and Labels	19-140-936
	Universal Combo Spill Kit	3 lb. Granular Sorbent, 2 lb. Each Acid and Base Neutralizing Powders, 1 Pair Goggles, 1 Pair Gloves, 1 Apron, 3 Dustpans, 3 Hand Brooms, 3 Spatulas, 2 Disposal Bags and Labels	19-140-941
	Flammable Solvent Spill Kit	3 lb. Granular Sorbent, 1 Pair Goggles, 1 Pair Gloves, 1 Apron, 1 Dustpan, 1 Hand Broom, 1 Spatula, 2 Disposal Bags and Labels	19-140-942

Chemical Spill Kits

	Description	Includes	Cat. No.
	Mini Chemical Spill Kit	3 lb. Granular Absorbent, 1 pr. Gloves, 1 Apron, 1 Dustpan, 1 Hand Broom, 1 Spatula, 1 Disposal Bag	19-140-933
	6.5 Gallon Chemical Spill Kit	10 Pads (15 x 19 in.), 3 SOCs (3 in. x 12 ft.), 1 Pair Gloves, 1 Disposal Bag	19-140-939
	17 Gallon Chemical Spill Kit	12 Pads (15 X 19 In.), 3 SOCs (3 In. X 12 Ft.), 2 Pillows (18 X 18 In.), 1 Pair Goggles, 1 Pair Gloves, 3 Disposal Bags	19-140-937
	55 Gallon Chemical Spill Kit	50 Pads (15 X 19 In.), 4 SOCs (3 In. X 12 Ft.), 8 Pillows (18 X 18 In.), 1 Pair Goggles, 1 Pair Gloves, 5 Disposal Bags	19-140-938
	75 Gallon Chemical Spill Kit	110 Pads (15 x 19 in.), 8 SOCs (3 in. x 12 ft.), 12 SOCs (3 in. x 4 ft.), 8 Pillows (18 x 18 in.), 1 Pair Goggles, 1 Pair Gloves, 10 Disposal Bags	19-140-940
	Chemical Spill Cabinet	5 Pillows (9 x 9 in.), 6 SOCs (3 in. x 12 ft.), 1 Pair Goggles, 1 Pair Gloves, 1 Dustpan, 1 Hand Broom, 1 Spatula, 1 Disposal Bag	19-140-934

Visit fishersci.com/fisherbrand or fishersci.ca/fisherbrand to view our full collection of Fisherbrand products..

Distributed by Fisher Scientific. Contact us today:

In the United States

Order online: fishersci.com

Call customer service: 1-800-766-7000

In Canada

Order online: fishersci.ca

Call customer service: 1-800-234-7437

