🕀 microman[®] 🔳

NEW Positive-Displacement Pipette for viscous, volatile, and problem liquids

Full range of Volumes

Model	Part Number	Volume Range	Price
M10E	FD10001G	1 - 10 μL	\$350
M25E	FD10002G	3 - 25 μL	\$350
M50E	FD10003G	20 - 50 μL	\$350
M100E	FD10004G	10 - 100 μL	\$350
M250E	FD10005G	50 - 250 μL	\$350
M1000E	FD10006G	100 - 1000 μL	\$350



	Model	Part Number	Volume Range	Tips per Box	Price
	CP10ST	F148413G	1 - 10 μL	192	\$88.00
•	CP10ST	F148313G	1 - 10 μL	960	\$377.00
	CP25ST NEW	F148712G	3 - 25 μL	576	\$255.00
	CP50ST NEW	F148713G	20 - 50 μL	576	\$255.00
	CP100ST	F148415G	10 - 100 μL	192	\$88.00
	CP100ST	F148315G	10 - 100 μL	960	\$377.00
	CP250ST NEW	F148714G	50 - 250 μL	576	\$255.00
	CP1000ST	F148180G	100 - 1000 μL	182	\$88.00





For customer service, call 1-800-766-7000. To fax an order, use 1-800-926-1166. To order online: www.fishersci.com

sales@gilson.com | 800-445-7661 www.gilson.com

NEW

NEW

NEW

NEW

NEW

M_{3N}





QuickSnap tip fitting

- Volume-securing switch
- Easy-to-read volume
- Improved handle shape
- Larger push button

New **QuickSnap tip fitting** for easy & instant tip application! MICROMAN[®] E is the only positive displacement pipette as intuitive and simple to fit as regular pipettes and tips.

Repositioned volumeter — an enhancement from classic MICROMAN, volume setting can be read on front of pipette, for easy view while aspirating and dispensing.

New Volume-Securing Switch allows for easy volume adjustment and minimizes the risk of accidentally changing volume during pipetting!

What are

pipettes?

positive-displacement

Recommended for problem samples

(viscous, dense, volatile, radioactive,

Direct contact of the piston with

Disposable piston (not a permanent

the sample (no air cushion).

part of the pipette)

Three things to remember

corrosive).

3

New **Improved handle Shape** with extended hook allows pipette to rest in the hand comfortably and securely. Larger **Push Button** provides easy access and better control.






Questions? Feedback? We would love to hear from you. techsupport@pipetman.com customersupport@pipetman.com 800-445-7661

What are air-displacement pipettes?

Three things to remember

- Recommended for aqueous samples and for general laboratory work.
 Always have a cushion of air (dead
- 2 volume) between the pipette piston and the liquid sample.
- **3** The piston is a permanent part of the pipette.





What can I pipette?

With MICROMAN [®] E, you may pipette everything you do with a standard pipette, PLUS:

- Oils
- Glycerol
- Blood
- RNA/DNA
- Radioactive samples
- Cosmetics



For customer service, call 1-800-766-7000. To fax an order, use 1-800-926-1166. To order online: www.fishersci.com

sales@gilson.com | 800-445-7661 www.gilson.com

