

# HandPRO™ Cleanroom & Specialty Glove Comparison Chart



Glove Style with Fisher Cat. No.	Thickness (Typical Values)	Length	Color	ISO 4	ISO 5	ISO 6-8	Nitrile	LOW DERMA™ Accelerator-Free Nitrile	Latex	Vinyl	Sterile
<b>HandPRO® 9300</b> 17-900-900 to 17-900-905 (XS-XXL)	Palm: 3.9 - 4.3 mils Finger: 5.5 - 6.2 mils	12"	White	X				X			
<b>HandPRO® 9100</b> 19-423-100 to 19-423-105 (XS-XXL)	Palm: 3.9 - 4.3 mils Finger: 5.5 - 6.2 mils	12"	White		X			X			
<b>HandPRO® 8750</b> 17-900-906 to 17-900-911 (XS-XXL)	Palm: 5.5 mils Finger: 8.2 mils	12"	Blue		X		X				
<b>HandPRO® 7100</b> 19-423-022 (XS) 19-423-024 to 19-423-027 (S-XL)	Palm: 4.3 mils Finger: 5.9 mils	12"	White		X		X				
<b>HandPRO® 7900</b> 17-900-933 to 17-900-937 (XS-XL)	Palm: 3.9 - 4.3 mils Finger: 5.5 - 6.2 mils	12"	White			X		X			
<b>HandPRO® 2400</b> 19-423-107 to 19-423-110 (S-XL)	Palm: 7.0 mils Finger: 7.8 mils	12"	Natural						X		
<b>HandPRO® 1700</b> 19-423-029 to 19-423-033 (XS-XL)	Palm: 3.1 - 3.5 mils Finger: 4.7 - 5.1 mils	9"	White			X	X				
<b>HandPRO® 1750</b> 17-500-100 to 17-500-105 (XS-XXL)	Palm: 2.3 - 2.7 mils Finger: 3.9 - 5.1 mils	9"	Blue			X		X			
<b>HandPRO® 1550</b> 19-423-034 to 19-423-037 (S-XL)	Palm: 3.1 mils Finger: 4.3 mils	12"	Clear		X					X	
<b>HandPRO® 550</b> 18-040-1266 to 18-040-1269 (X-XL)	Palm: 3.1 mils Finger: 3.1 mils	9"	Clear			X				X	
<b>HandPRO® 617200</b> 17-623-649 to 17-623-654 (XS-XXL)	Palm: 4.7 mils Finger: 5.5 mils	16"	White		X		X				X
<b>HandPRO® 6200</b> 17-623-643 to 17-623-648 (XS-XXL)	Palm: 4.7 mils Finger: 5.5 mils	16"	White		X		X				
<b>HandPRO® P3 4511</b> 17-900-920 to 17-900-926 (6.0-9.0)	Palm: 7.8 mils Finger: 8.6 mils	12" Hand Specific	Natural		X				X		X

Hourglass-Intl.com  
800-277-0994

*"Your Protection Is Our Purpose"*

Find it at [fishersci.com](http://fishersci.com) and [fishersci.ca](http://fishersci.ca)

