

# Hazard Communication

Find the essential items you need to comply with updates to the Hazard Communication Standard (HCS), established by the Occupational Safety and Health Administration (OSHA).



**Safety**

Protecting What Matters Most

The HCS has been aligned with the Globally Harmonized System of Classification and Labeling of Chemicals (GHS) to provide a common and coherent approach to classifying chemicals and communicating hazard information via labels and safety data sheets.

## Hazard Communication Standard

To support chemical safety in the workplace, all workers must have access to information about the identities and hazards of chemicals with which they come into contact. The HCS requires that this information be developed and disseminated:

- Chemical manufacturers and importers must evaluate the hazards associated with the chemicals they produce or import and prepare labels and safety data sheets to convey that information to their customers
  - Specific criteria are used to classify health and physical hazards of chemicals and chemical mixtures
  - Safety Data Sheets (SDS) require a specified 16-section format
  - Labels must include a harmonized signal-word, pictogram and a hazard statement for each hazard class and category, plus precautionary statements
- Employers who keep potentially hazardous chemicals in the workplace must label those chemicals and provide safety data sheets for any exposed workers
  - Employers must train employees about the new label elements and safety data sheet format to facilitate recognition and understanding
  - Employers must train employees to appropriately handle hazardous chemicals

## Right to Know (RTK) and Global Harmonized System (GHS) Compliance Products



Product Description	Type	Language	Display Material	Dimensions: H x W x D	Cat. No.
Brady™ Right-to-Know Compliance Centers, Single or Double Displays, with or without SDS Binders, English or Spanish Languages, Yellow and Red	Single, 1 Binder	English	Polystyrene	20 x 14 x 4.5 in. (50.8 x 35.5 x 11.4 cm)	<b>19-103-279</b>
	Single, 1 Binder	Spanish	Polystyrene		<b>19-103-282</b>
	Single with Inserts	English	Polystyrene		<b>19-103-285</b>
	Single, No Binder	English	Polystyrene		<b>19-103-250</b>
	Single, 2 Binders	English	Polystyrene		<b>19-103-274</b>
	Double, 2 Binders	English	Polystyrene	20 x 29 x 4.5 in. (50.8 x 73.6 x 11.4 cm)	<b>19-103-280</b>
	Double, 2 Binders	English	Polystyrene		<b>19-103-287</b>
ZING™ Enterprises SDS Station Kit, Single or Double Displays, Wall Mount (Corner Holes), English and Spanish Versions, Red and White	Economy Station	English	Plastic	14 x 4 in. (35.5 x 10 cm)	<b>18-002-998</b>
	Single Station	English	Aluminum	20 x 5.25 in. (51 x 13.3 cm)	<b>18-003-001</b>
	Double Station	English	Aluminum	28 x 5.25 in. (71 x 13.3 cm)	<b>18-003-003</b>
	Training Station	English	Aluminum	28 x 5.25 in. (71 x 13.3 cm)	<b>18-003-005</b>
	Single Station	Bilingual*	Aluminum	20 x 5.25 in. (51 x 13.3 cm)	<b>18-003-007</b>
	Double Station	Bilingual*	Aluminum	28 x 5.25 in. (71 x 13.3 cm)	<b>18-003-009</b>
	Training Station	Bilingual*	Aluminum	28 x 5.25 in. (71 x 13.3 cm)	<b>18-003-011</b>
ZING™ Enterprises SDS Training Booklets, 10/Pack		English	Paper	8.5 x 5.5 in. (21.6 x 14 cm)	<b>18-002-999</b>
ZING™ Enterprises GHS Introduction Poster, Red on White		English	Recycled Plastic	24 x 18 in. (61 x 46 cm)	<b>18-002-994</b>

\* English and Spanish

## RTK, NFPA, HMIG, and Other Hazard Labels




Description	Dimensions	Material	Quantity	Cat. No.
Brady™ Right-to-Know Labels, Write-On, White with Color-Printed NFPA Diamond	2.875 x 5 in. (7.3 x 12.7 cm)	Vinyl	250/Pack	<b>19-016-217</b>
	3 x 5 in. (7.6 x 12.7 cm)	Vinyl	250/Pack	<b>19-016-346</b>
	2.5 x 2.5 in. (6.4 x 6.4 cm)	Vinyl	250/Pack	<b>19-016-345</b>
Brady™ Write-On Right-To-Know Laboratory Labels, White with HMIG* Printed in Color	1.25 x 2 in. (3.2 x 5.2 cm)	Paper	500/Pack	<b>19-107-227</b>
	1.25 x 2 in. (3.2 x 5.2 cm)	Vinyl	500/Pack	<b>19-110-332</b>
	5.75 x 5.75 in.	Vinyl	25/Pack	<b>19-112-750</b>
	4 x 4 in. (10.4 x 10.4 cm)	Vinyl	25/Pack	<b>19-112-751</b>
	2 x 2 in. (5.2 x 5.2 cm)	Vinyl	25/Pack	<b>19-112-752</b>
	1 x 1 in. (2.5 x 2.5 cm)	Vinyl	25/Pack	<b>19-112-753</b>
National Marker™ Write-On Hazard Warning Labels, NFPA Format	1 x 3 in. (2.5 x 7.6 cm)	Paper	500/Pack	<b>17-986-90C</b>
Brady™ Write-On Container Labels, Blank with HMIG Color Bar	5 x 3 in. (12.7 x 7.9 cm)	Paper	500/Pack	<b>19-112-926</b>
Brady™ Write-On Container Labels, Blank, NFPA Color Bar Format	5 x 3 in. (12.7 x 7.9 cm)	Paper	500/Pack	<b>19-112-929</b>
Brady™ HMIG Labels, White with Color Printing	5.875 x 4 in. (15 x 10 cm)	Paper	100/Pack	<b>19-110-406</b>
	1.5 x 3.875 in. (3.8 x 9.8 cm)	Paper	1,000/Pack	<b>19-823-719</b>
Accuform™ Signs NFPA Classification Labels, Temperature Range: -40°C to +121°C (-40 to 250°F), Paper or Polyester	4 x 4 in. (10.4 x 10.4 cm)	Paper	500/Pack	<b>19-121-462</b>
	4 x 4 in. (10.4 x 10.4 cm)	Polyester	500/Pack	<b>19-121-463</b>
	6 x 6 in. (15.2 x 15.2 cm)	Paper	500/Pack	<b>19-121-464</b>
	6 x 6 in. (15.2 x 15.2 cm)	Polyester	500/Pack	<b>19-121-465</b>
	1.5 x 3.875 in. (3.8 x 9.8 cm)	Polyester	500/Pack	<b>19-804-607</b>
	1.5 x 3.875 in. (3.8 x 9.8 cm)	Paper	500/Pack	<b>19-804-609</b>
Accuform™ Signs HMCIS Labels	1.5 x 3.875 in. (3.8 x 9.8 cm)	Paper	500/Pack	<b>19-804-621</b>
Accuform™ Signs NFPA Diamond Labels	2 x 2 in. (5.2 x 5.2 cm)	Paper	250/Pack	<b>19-121-454</b>
			500/Pack	<b>19-804-613</b>
	2 x 2 in. (5.2 x 5.2 cm)	Polyester	250/Pack	<b>19-121-455</b>
			500/Pack	<b>19-804-611</b>
	4 x 4 in. (10.4 x 10.4 cm)	Paper	250/Pack	<b>19-121-456</b>
			500/Pack	<b>9-804-614</b>
	4 x 4 in. (10.4 x 10.4 cm)	Polyester	250/Pack	<b>19-121-457</b>
			500/Pack	<b>19-804-616</b>
	6 x 6 in. (15.2 x 15.2 cm)	Paper	250/Pack	<b>19-121-458</b>
	6 x 6 in. (15.2 x 15.2 cm)	Polyester	250/Pack	<b>19-121-459</b>
			500/Pack	<b>19-804-615</b>

\* Hazardous Materials Identification Guide



## RTK, NFPA, HMIG, and Other Hazard Labels (cont.)



Description	Dimensions	Material	Quantity	Cat. No.
Brady™ NFPA Diamond Labels, White Vinyl with Color Printing	15 x 15 in. (38.1 x 38.1 cm)	Vinyl	10/Pack	<b>19-110-396</b>
National Marker™ Write-On NFPA Labels, White Paper with Color Printing	2 x 2 in. (5.2 x 5.2 cm)	Paper	250/Pack	<b>17-981-63A</b>
	4 x 4 in. (10.4 x 10.4 cm)	Paper	250/Pack	<b>17-981-63B</b>
Accuform™ Signs DOT Shipping Labels, Text: Flammable Liquid 3, White on Red	4 x 4 in. (10 x 10 cm)	Vinyl	Each	<b>19-804-962</b>
Accuform™ Signs DOT Shipping Labels, Text: Flammable Liquid 2, White on Red	4 x 4 in. (10 x 10 cm)	Paper	250/Pack	<b>19-809-835</b>
Accuform™ Signs DOT Shipping Labels, Text: Flammable Liquid 3, White on Red	4 x 4 in. (10 x 10 cm)	Paper	250/Pack	<b>19-809-836</b>
Accuform™ Signs DOT Shipping Labels, Text: Corrosive 8, Black on White	4 x 4 in. (10 x 10 cm)	Paper	250/Pack	<b>19-809-837</b>
Brady™ Hazardous Material Shipping Labels, Text: Flammable Liquid 3, White on Red	4 x 4 in. (10 x 10 cm)	Vinyl	Each	<b>19-110-966</b>

\* Hazardous Materials Identification Guide

## Safety Showers and Emergency Eye Washes



### Drench and Combination Safety Showers

Description	Mounting	Dimensions: H x W x D	Cat. No.
Hughes Laboratory Drench Showers*, Pressure Range: 22 to 87 psi, Powder-Coated SS, Green	Wall	10 x 36 x 12 in. (25 x 91 x 30.5 cm)	<b>18-666-672</b>
	Ceiling	14 x 26 x 14 in. (35.6 x 66 x 35.6 cm)	<b>18-666-673</b>
	Ring Main	14 x 26 x 14 in. (35.6 x 66 x 35.6 cm)	<b>18-666-674</b>
	Wall	52 x 12 x 12 in. (132 x 30.5 x 30.5 cm)	<b>18-666-675</b>
Hughes Laboratory Combination Shower and Eyewash*, Pressure Range: 22 to 87 psi; 3 gal./min. Flow Rate, Powder-Coated SS, Green, Open ABS bowl	Floor	48 x 16 x 16 in. (122 x 40.6 x 40.5 cm)	<b>18-666-676</b>

\* Meet ANSI Z358.1 2014 and EN 15154 standards and support OSHA requirements



## Safety Showers and Emergency Eye Washes



### Safety Eyewashes

Description	Color	Capacity	Dimensions: H x W x D	Quantity	Cat. No.
Hughes Gravity-Fed Eyewash Stations*, Flow Rate: 2 L/min. (0.55 gal./min.), Wall-Mount or Free-Standing	Orange	10 gal. (38 L)	29.5 x 18 x 7 in. (75 x 46 x 18.4 cm)	Each	<b>19-121-135</b>
	Green	16 gal. (60.5 L)	25 x 21 x 11.3 in. (64 x 54 x 29 cm)	20/Case	<b>19-141-120</b>
				Each	<b>19-111-121</b>
Hughes Wall-Mounted Eye/Face Wash*, SS with ABS Bowl, Pressure Range: 29 to 97 psi	Multi	Flow Rate: 3 gal./min.	16 x 18 in. (40.6 x 45.7 cm)	12/Pack	<b>19-111-122</b>
				Each	<b>18-666-640</b>
				Each	<b>18-666-643</b>

\* Meet ANSI and EN15154 standards and support OSHA requirements



### Inspection and Lockout-Tagout Tags

Description	Material (Thickness)	Dimensions	Quantity	Cat. No.
Accuform™ Signs Emergency Shower and Eyewash Record Tags, Green/Black on White	RP Plastic (15 mil)	5.75 x 3.25 in. (14.6 x 8.25 cm)	25/Pack	<b>19-804-815</b>
	PF Cardstock (10 mil)		25/Pack	<b>19-804-814</b>
Brady™ Emergency Shower/Eyewash Inspection Tag, Test Record, Green on White	Polyester (0.36 mm)	5.75 x 3 in. (14.6 x 7.6 cm)	10/Pack	<b>19-133-789</b>
Brady™ Emergency Shower/Eyewash Inspection Tag and Test Record, Green on White	Polyester (0.51 to 0.64 mm)	5.9 x 3 in. (15 x 8 cm)	10/Pack	<b>19-040-386</b>
	Cardstock (0.51 to 0.64 mm)	7 x 4 in. (18 x 10 cm)	10/Pack	<b>19-040-402</b>
			100/Pack	<b>19-040-846</b>
Justrite™ Equipment Inspection Record, For Safety Showers and Eyewashes	Plastic	3 x 15 in. (7.6 x 38 cm)	Each	<b>18-666-723</b>
Brady™ Hazardous Exposure Tags, "Target Organs Affected" on Reverse Side	Polyester	5.75 x 3 in. (14.6 x 7.6 cm)	25/Pack	<b>19-080-737</b>
Brady™ Right-to-Know Accident Lockout Tags, Blank on Reverse Side	Polyester	5.75 x 3 in. (14.6 x 7.6 cm)	25/Pack	<b>19-102-664</b>

Browse our full collection of safety products at [fisherhealthcare.com](https://fisherhealthcare.com).

Distributed by Fisher Healthcare. Contact us today:

#### In the United States

Order online: [fisherhealthcare.com](https://fisherhealthcare.com)

Fax an order: 1-800-290-0290

Call customer service: 1-800-640-0640

