

accu-jet[®] S Pipette Controller



New!



- Simple:** Enhanced comfort and precise control for delicate cell culture work
- Easy:** Adjustable power and precision at your fingertips
- Efficient:** Keep pipettes clean & sterile with integrated rest position



It Stands Alone

The NEW accu-jet[®] S pipette controller stands alone as a versatile and well-balanced addition to your lab.

It makes lab work simple, easy and efficient, whether you use it for cell culture work, reagent preparation, or general pipetting.

Adjust power and precision on the fly, with pressure sensitive buttons that smoothly control pipetting speed, and achieve precise meniscus control when used with pipettes as small as 0.1 mL. The new well-balanced design features an ergonomic

grip for comfortable uninterrupted use, and the integrated rest position lets you put it down without sacrificing the cleanliness or sterility of your serological pipette.

A wall mount also provides additional storage, freeing up space on your work area for disinfection or decontamination tasks. It's quick and convenient, and ready when you are.

accu-jet[®] S pipette controller - (100-240 V/50-60 Hz)

BrandTech [®] Cat. No.	Fisher Scientific Cat. No.	Color
26350	13-689-549	anthracite
26351	13-689-546	berry
26352	13-689-547	petrol
26353	13-689-548	amethyst

Universal AC adapter included



Efficient single-handed operation



Wall mount for space-saving storage

Membrane filters for accu-jet[®] S pipette controller

Description	Pack of	BrandTech [®] Cat. No.	Fisher Scientific Cat. No.
0.2 µm, sterile	1	26530	04-977-158
0.2 µm	10	26535	04-977-157
3 µm	1	26052	13-688-300
3 µm	10	26056	21-381-237

Find it at fishersci.com and fishersci.ca



accu-jet[®] S Pipette Controller



Accu-jet[®] S Highlights

- For glass and plastic pipettes from 0.1 to 200 mL
- Four attractive colors
- Two color charge indicator LED/light
- NiMH battery with intelligent charging technology lasts up to 8 hours.
- Ergonomic handgrip with a lightweight, well-balanced design
- Quick: Fills a 25 mL pipette at maximum motor speed in only 3 seconds
- Adapter, adapter housing and filter are autoclavable



Charging indicator

Bright LED visually indicates battery capacity. Get 8 hours from a fully charged battery, LED turns red when 2 hours of charge remains.

Mode selection

Gravity delivery or blow-out with motor power

Variable motor speed

Smooth control of the pipetting speed

Pipette adapter

Firmly holds pipettes and provides protection against over-aspiration.

Pipetting buttons

Precise and continuous liquid aspiration and dispensing

Charging socket

NiMH battery is fully charged in just 4 hours. Working during the charging process is also possible with the charging cable connected.



Rest position with inserted pipette

[Watch the product video of the new accu-jet[®] S](#)



Gravity delivery or blow-out with motor power



Direct outlet of sample vapors



Membrane filter and check valve prevent liquid penetration and over-aspirating liquid



Smart charging technology prevents lazy battery effect

Distributed by Fisher Scientific. Contact us today:

In the United States

Order online: fishersci.com
Call customer service: 1-800-766-7000

In Canada

Order online: fishersci.ca
Call customer service: 1-800-234-7437

