

Laboratory Evaporation GlasswareDecades of expertise in glass manufacturing

Original BUCHI glassware guarantees the highest levels of efficiency and safety thanks to outstanding precision in manufacturing. For more than 80 years BUCHI has been manufacturing innovative and durable glass parts to ease daily laboratory work.







Glassware made by BUCHI

Benefit from high quality and precision

The BUCHI experience in glass manufacturing results in glassware of outstanding quality and guarantees highest safety and increased efficiency due to our exacting standards of accuracy.

Benefits of BUCHI glassware



High efficiency

- · Maximized vacuum stability thanks to very tight joints
- · Optimum heat transmission due to optimized wall thickness of evaporating flasks
- · High evaporating performance due to pear-shaped evaporating flask
- · High throughput due to advanced design of condensers



Maximized safety

- · Use of highly resistant glass provides high levels of safety
- · Guaranteed leak-tightness and protection against hazardous fumes thanks to high precision joints
- · Maximum stability thanks to sophisticated PLASTIC+GLAS coating



Proven reliability

- · More than 80 years of experience in glass manufacturing
- · Durable products made with best quality raw materials
- · Developed and manufactured by experienced and committed employees

Laboratory evaporation glassware quality facts



High quality materials

- · Exclusive use of DURAN® borosilicate glass 3.3
- · High chemical resistance against acids, alkalis and organic substances
- · Resistant to thermal shocks and high temperatures combined with low thermal expansion



Accuracy

- · Constant monitoring of glass wall thickness uniformity
- · High degree of attention paid to sphericity of rotating glass parts
- · Glass parts are tension-relieved at 560 °C



Expertise

- · Unique machines developed in-house to automate repetitive manufacturing processes in order to guarantee a high level of reproducibility
- · Many decades of experience guarantee top quality glass parts

"PLASTIC+GLAS" coating



Maximized safety

- · Protects users from contact with chemicals in case of glass breakage
- · Avoids risk of injuries when touching broken glass
- · Prevents glass splitter impacts in case of implosions

Improved sturdiness

- · Protects glassware from physical damage
- · Chemical resistant high quality coating

Retention of substances

- · Retains valuable substance in case of glass breakage
- · Valuable sample or toxic solvent vapors remain within glassware

P+G properties



For standard applications. Available for condensers, evaporating and receiving flasks. Operating range: -30 to 60 $^{\circ}\text{C}$



Low temperature receiving flasks are used for cold trap and other low temperature applications. Operating range: -70 to 40 $^{\circ}\text{C}$



Wide range of high quality BUCHI glassware

For any rotary evaporator

Evaporating flasks

High performance pear-shaped flasks for distillation of solvents.



Evaporating flask



Evaporating flask, 5 L

Flask size	29/32	24/40	24/29	29/42
50 mL	000431	008750	000472	008736
50 mL P+G	033405			
50 mL P+G-LT*	11066585			
100 mL	000432	008751	000473	008737
100 mL P+G	033404			
100 mL P+G-LT*	11066586			
250 mL	000433	008754	008753	008738
250 mL P+G	025520			
250 mL P+G-LT*	11066587			
500 mL	000434	008758		008739
500 mL P+G	025322	025261		
500 mL P+G-LT*	11066588			
1000 mL	000435	000440	008761	008762
1000 mL P+G	020729	020730		025517
1000 mL P+G-LT*	11066589			
1000 mL brown	11069664	11069667		
2000 mL	000436	008765	008764	008769
2000 mL P+G	025323	025262		
2000 mL brown	11069665	11069668		
3000 mL	000437	008767		008770
3000 mL P+G	025324	025263		027346
3000 mL brown	11069666	11069669		
4000 mL	047991	047990		
4000 mL P+G	047993	047992		
5000 mL ¹	046573	046586		
5000 mL P+G ¹	046583	046596		

^{&#}x27;Spherical

Drying flasks

Pear shaped flasks with indents for increased efficiency in powder drying by reducing accumulations on the glass walls.



Drying flask

Flask size	29/32	24/40
500 mL	000452	011579
1000 mL	000453	000420
2000 mL	000454	011580

^{*}Evaporating flasks with low temperature P+G-LT coating for freeze drying applications with Dewar container. Operating range from -70°C to 40°C.

Beaker flasks

Beaker flasks with large screw-cap opening for easy retrieval of substances. Drying beaker flask consists of notches for increased efficiency in powder drying. Both variations can be used in the temperature range from -40 to 100 °C.



Round bottom / Drying



Pear shape

Max. gross weight (beaker flask + sample) allowed is 3 kg

	For evaporation		For dry	ng	
Flask size	29/32	24/40	29/32	24/40	
500 mL ¹ Convex bottom (Ø=75 mm)	11063154	11063155	11063158	11063159	
1500 mL ² Convex bottom (Ø=110 mm)	11063156	11063157	11063160	11063161	
1500 mL ² Round bottom (Ø=110 mm)	11065718	11065719	-	-	
4000 mL Pear shape (Ø=110 mm)	11065690	11065691	-	-	
¹ Working volume of 150	mL ² Working vol	ume of 450 mL Ø=	Diameter of the flask	c opening	
Spare beaker flasks	500 mL ¹ Convex bottom (Ø=75 mm)	1500 mL ² Convex bottom (Ø=110 mm)	1500 mL ² Round bottom (Ø=110 mm)	4000 mL Pear shape (Ø=110 mm)	
For evaporation	11059185	11059186	11065716	11065689	
For drying	11059268	11059269	-	-	

Receiving flasks

Spherical flasks with ball joint (35/20) for collecting the condensed solvents.



Receiving flask

Flask size	Standard	P+G	P+G-LT
50 mL	000421		
100 mL	000422		
250 mL	000423	11060907	11060908
500 mL	000424	025264	040774
1000 mL	000425	020728	040775
2000 mL	000426	025265	040776
3000 mL	000427	025266	040777

Flask holder

Holder for 50 mL to 5000 mL evaporating and receiving flasks.



Flask holder

1	048618
5	11059916



Rotavapor® accessories

Wide range of glassware and accessories

Vapor ducts

Glass parts to connect the evaporating flask to the Rotavapor®. All vapor ducts include the Combi-Clip to fasten the evaporating flask.



Vapor duct



R-300, R-215, R-210, R II (with Combi-Clip*) Compatible with

glass assembly	29/32	24/40	29/42	24/29
А	11062267	11062268	11062269	
V, HP, C, S, E, CR, BY	11062186	11062187	11062464	11062909
V, HP, C (analytical)	11062465	11062466	11062467	
For high temperatures, short Combi clip, vapor duct HT, ring NS 34/32 on 30/32	11061837			
Vapor duct with frit SJ29/32, incl. Combi-Clip For powder drying. To prevent powder from getting into the condenser. For glass assembly V, HP, C, S, E, BY and CR.	11057297			

^{*}Single Combi-Clip: 11059770



R-100, R-3, R-3000, R-144, R-134, R-124, R-114 Compatible with glass assembly 29/32 24/40

Vapor ducts

V and C 032339 032341

Vacuum seals

Air-tight lip seals between the rotating vapor duct and the condenser.



Vacuum seal

Compatibility	Vacuum seal	
*R-300, R-215, R-210, R II	VS26, PTFE base, NBR O-ring ¹	11069167
R-100, R-3	KD22, seal PTFE	000636
R-100, R-3	KD22, seal PTFE ¹	11056622

Stopcocks

Glass parts for aerating the Rotavapor® system.



Stopcock	18.8/38
Standard stopcock	040627
Stopcock, Analytic, PTFE/25% glass fiber, SJ18.8/38	11069607
For condenser C/CR, glass, SJ18.8/38 For aeration of the system. For cold trap outer part.	040628
PTFE, incl. 3-way valve	11058814

¹FDA-compliant sealing material *Recommended for analytical purposes

Bump trap adapters

Glass adapters for excessively-foaming samples. Prevents foam from entering the vapor duct and condenser.




Distillation spiders

Glass parts for simultaneous distillation in 5, 6, 12 or 20 distilling flasks (cross contamination possible). Please refer to the BUCHI "Parallel Evaporation Solutions" brochure for highly efficient parallel evaporation without cross contamination.



Spider with evaporating flasks

Spider with evaporating flasks	29/32 ¹	24/40 ¹	24/29 ²
Spider with 5 x 50 mL flasks (24/29)	001332	011574	
Spider with 5 x 100 mL flasks (24/29)	001333	011575	
1 x 50 mL evaporating flask (without spider)			000472
1 x 100 mL evaporating flask (without spider)			000473



Spider with cylindric flasks

Spider with cylindric flasks	29/32 ¹	14/23 ²
Spider with 6 x 20 mL cylindric flasks (14/23)	001334	
Spider with 12 x 20 mL cylindric flasks (14/23)	001335	
Spider with 20 x 20 mL cylindric flasks (14/23)	001336	
1 x 20 mL cylindric flask (without spider)		000477
1 2		

Joint of the spider to vapor duct Joint of the flask to spider

Intermediate piece



Intermediate piece with valve



Connection piece with 3-way valve, placed between the condenser and the receiving flask. Allows to remove and empty the receiving flask during evaporating process.

11063430

Combining the Multivapor™ with the Rotavapor® requires a T-shaped glass connector for the condenser of the rotary evaporator. The T-piece consist of two spherical joints for the condenser assembly and a SVL 22 joint for the vacuum tube. The length of the tube is 400 mm.

048740

Spherical flask with ball joint (35/20) and with manual drain valve for draining after aeration without removal of receiving flask.



Flask size	P+G
1000 mL	036919

Receiving flask with drain valve




Rotavapor® glass assemblies Widest range of highly efficient condensers

74	ns o	7	nz				The state of the s	
	А	С	V	S	CR	E	BY	HP
Applications	Diagonal	Cold trap	Vertical	Reflux	Cold trap reflux	Expansion	Double jacket	High per- formance
Distillation	•	•	•	•	•	•	•	•
Drying	•	•	•	•	•	•	•	•
Concentration	•	•	•	•	•	•	•	•
Reflux reaction				•	•		•	
Soxhlet extraction				•			•	
Re-crystallization	•	•	•	•	•	•	•	•
Solvent/Sample pro	perties							
Boiling point range	M – H	L-M	M – H	M – H	L – M	М – Н	М – Н	L – H
Bumping or foaming	•1	•1	•1	•1	•1	•	•1	•1
Characteristics								
Cooling	CL	CM	CL	CL	CM	CL	CL	CL
Cooling temperature range	Н	М	Н	Н	М	Н	Н	Н
Suitable for high throughput	•		•	•		•	•	•
Vapor temperature sensor			Available	Available		Available	Available	Available
Foam sensor		•	•					•
Automatic distillation			•2	•2				•2
Suitable for limited space	VS	HS	HS	HS	HS	HS	HS	HS
Condenser surface max. [cm²]	1500	500	1500	1500	500	1500	1300	3000
Available for R-300	•	•	•	•	•	•	•	•
Available for R-100		•	•3					

$$[\]label{eq:hamiltonian} \begin{split} H = & \mbox{ High } \mbox{ M = Medium } \mbox{ L = Low } \mbox{ VS = Limited vertical space } \mbox{ HS = Limited horizontal space } \\ CL = & \mbox{ Cooling liquid } \mbox{ CM = Coolant mixtures (e.g. dry-ice/acetone)} \\ ^{1} & \mbox{ With Reitmeyer adapter } \mbox{ }^{2} \mbox{ Possible with AutoDest sensor only } \mbox{ }^{3} \mbox{ Limited features} \end{split}$$

Vertical (V) condenser

The following features displayed are only applicable to the condenser compatible to the Rotavapor® R-300.



Glass assemblies

All glass assemblies include a 1 liter receiving flask, the required tubings and a ball joint clamp. Evaporating flask, vacuum seal, vapor duct and condenser holder are not included.

	R-1	00				R-3	300			
Characteristics	V	С	Α	V	С	CR	S	E	BY	HP
Top inlet	•		•	•			•	•	•	•
Inner glass tube				•			•			•
Stopcock (feeding possible)	•	•	•	•	•	•	•	•	•	•
Inner glass plate				•						•
Connector for vapor temperature sensor				•			•	•	•	•
Condenser holder*	052893	052893		048180	048180	048180	048180	included	048180	included (048180)
Condensate trap				•						•

^{*}Optionally available

Part no. of glass assemblies

	V	С	Α	CR*	S*	E*	BY*	HP*
R-300, R-2xx	11062432	040640	048168	048292	048290	11061112		11066561
P+G: R-300, R-2xx	11062433	040642	048169	048293	048291	11061113	048297	11066562
RII	048172	040640	048170					
P+G: R II	048173	040642	048171					
R-100, R-3	11057056	040640						
P+G: R-100, R-3	11057057	040642						


^{*}Not compatible with R-100



Benefit from the market leader

Frequently asked questions

What is the chimney effect and how does it affect distillation efficiency?





Chimney effect


Turblence, forced condensation

By evaporation - changing of state from liquid to gas - the volume of the sample increases by a factor up to 20,000. In the condenser the gas is re-condensed to a liquid and the volume shrinks immediately. During this evaporation-condensation process, vapor velocity at narrow points of the glass apparatus can be up to 150 km/h.

Distillation efficiency can be significantly increased by reducing the so-called chimney effect.

In order to maximize turbulence inside the condenser, the vacuum is applied at the top middle, however, the vacuum connectors are below. This optimal construction maximizes the movement of vapor inside the condenser, thus preventing fumes escaping to the vacuum source.

Can the evaporation flask be fed via the condenser stopcock?








Screw cap

Yes, all condensers used for R-300, R-100, R-210, R-215 and R-3 allow feeding of the evaporation flask through the standard stopcock. The C- and A-condenser for R II consist of a screw-cap instead of a stopcock and therefore does not allow feeding; a stopcock for feeding is optionally available.

When is a 3000 cm² high performance condenser recommended?



High performance condenser is recommended in the following cases:

- For reduction of solvent emissions
- For operating at higher temperature difference (ΔΤ>20°C) and lower pressure values
- For distilling low boiling solvents
- If faster process and greater distillation rate are required

Are the condensers shown on the page 9 compatible with the older generation of BUCHI Rotavapor® product lines (R-215, R-210, R II, R-3)?

Yes, glass assemblies V, C, A, CR, S, E, HP and BY are compatible with the product lines R-300, R-210 and R-215 only. R-II product line is compatible with glass assemblies V, C and A. R-3 product line is compatible with V and C glass assemblies.


What factors influence glass shock temperature?

DURAN® borosilicate glass 3.3 is notable for its excellent temperature stability. The shock temperature is influenced by many stress factors which act cumulatively. Typical factors are tensions, vacuum, mechanical damage and shape as well as thickness of the respective glass part. Glass should be inspected visually prior to any use, especially when applying vacuums.

Are there differences between BUCHI and 3rd party evaporating flasks?

Yes, there may be several properties which set high quality BUCHI flasks apart: Optimized/uniform flask thickness, quality of joints and sphericity of the flask. All of these properties have an important impact on distillation efficiency.

What do the numbers "29/32" shown on previous pages mean?



The number-pair (e.g. 29/32) describes a joint size. The first number refers to the width of the joint (A). The second number (after the slash) refers to the length of the joint (B). 29/32 therefore means that the width of the joint is 29 mm and the length of the joint is 32 mm.

Can BUCHI provide customized glassware which is not listed in this document?

Yes, there is an additional extensive range of glassware available. BUCHI also offers customized glass according to your needs, for example amber glass for light-sensitive samples. For further information about our glassware range please contact your local BUCHI representative.

BUCHI Affiliates:

Europe

Switzerland/Austria

BÜCHI Labortechnik AG

CH – 9230 Flawil T +41 71 394 63 63 F +41 71 394 64 64 buchi@buchi.com www.buchi.com

Italy

BUCHI Italia s.r.l.

IT – 20010 Cornaredo (MI) T +39 02 824 50 11 F +39 02 575 12 855 italia@buchi.com www.buchi.com/it-it

Benelux

BÜCHI Labortechnik GmbH

Branch Office Benelux
NL – 3342 GT Hendrik-Ido-Ambacht
T +31 78 684 94 29
F +31 78 684 94 30
benelux@buchi.com
www.buchi.com/bx-en

Russia

BUCHI Russia/CIS

RU – 127006 Moscow T +7 495 36 36 495 russia@buchi.com www.buchi.com/ru-ru

France

BUCHI Sarl

FR – 91140 Villebon-sur-Yvette T +33 1 56 70 62 50 F +33 1 46 86 00 31 france@buchi.com www.buchi.com/fr-fr

Spair

BUCHI Ibérica S.L.U.

ES – 08960 Barcelona T +34 936 06 8010 iberica@buchi.com www.buchi.com/es-es

Germany

BÜCHI Labortechnik GmbH

DE – 45127 Essen T +800 414 0 414 0 (Toll Free) T +49 201 747 49 0 F +49 201 747 49 20 deutschland@buchi.com www.buchi.com/de-de

United Kingdom

BUCHI UK Ltd.

GB – Suffolk CB8 7SQ T +44 161 633 1000 F +44 161 633 1007 uk@buchi.com www.buchi.com/gb-en

NIR-Online

Germany

BÜCHI NIR-Online

DE - 69190 Walldorf T+49 6227 73 26 60 F+49 6227 73 26 70 nir-online@buchi.com www.nir-online.de

America

Brazil

BUCHI Brasil Ltda. BR – Valinhos SP 13271-200

T +55 19 3849 1201 F +55 19 3849 2907 brasil@buchi.com www.buchi.com/br-pt

USA/Canada

BUCHI Corporation

US – New Castle, DE 19720 T +1 877 692 8244 (Toll Free) T +1 302 652 3000 F +1 302 652 8777 us-sales@buchi.com www.buchi.com/us-en

Asia

China

BUCHI China

CN – 200233 Shanghai T +86 21 6280 3366 F +86 21 5230 8821 china@buchi.com www.buchi.com/cn-zh

India

BUCHI India Private Ltd.

IN – Mumbai 400 055 T +91 22 667 75400 F +91 22 667 18986 india@buchi.com www.buchi.com/in-en

Indonesia

PT. BUCHI Indonesia

ID – Tangerang 15332 T +62 21 2222 9478 F +62 21 5568 7906 indonesia@buchi.com www.buchi.com/id-in

Japan

Nihon BUCHI K.K.

JP – Tokyo 110-0008 T +81 3 3821 4777 F +81 3 3821 4555 nihon@buchi.com www.buchi.com/jp-ja

Korea

BUCHI Korea Inc.

KR - Seoul 153-782 T +82 2 6718 7500 F +82 2 6718 7599 korea@buchi.com www.buchi.com/kr-ko

Malaysia

BUCHI Malaysia Sdn. Bhd.

MY – 47301 Petaling Jaya, Selangor T +60 3 7832 0310 F +60 3 7832 0309 malaysia@buchi.com

www.buchi.com/mv-en

Singapore

BUCHI Singapore Pte. Ltd.

SG – Singapore 609919 T +65 6565 1175 F +65 6566 7047 singapore@buchi.com www.buchi.com/sg-en

Thailand

BUCHI (Thailand) Ltd.

TH – Bangkok 10600 T +66 2 862 08 51 F +66 2 862 08 54 thailand@buchi.com www.buchi.com/th-th

BUCHI Support Centers:

South East Asia

BUCHI (Thailand) Ltd.

TH-Bangkok 10600 T+66 2 862 08 51 F+66 2 862 08 54 bacc@buchi.com www.buchi.com/th-th

Middle East

BÜCHI Labortechnik AG

UAE – Dubai T +971 4 313 2860 F +971 4 313 2861 middleeast@buchi.com www.buchi.com

Latin America

BUCHI Latinoamérica S. de R.L. de C.V.

MX – Mexico City T +52 55 9001 5386 latinoamerica@buchi.com www.buchi.com/es-es

We are represented by more than 100 distribution partners worldwide. Find your local representative at: www.buchi.com

Distributed by Fisher Scientific. Contact us today:

In the United States

Order online: fishersci.com
Fax an order: 1-800-926-1166
Call customer service: 1-800-766-7000

In Canada

Order online: fishersci.ca Fax an order: 1-800-463-2996 Call customer service: 1-800-234-7437

