

FACT SHEET FOR HEALTHCARE PROVIDERS

ID NOW COVID-19 - Abbott Diagnostics Scarborough, Inc.

Updated: June 1, 2020

Coronavirus
Disease 2019
(COVID-19)

This Fact Sheet informs you of the significant known and potential risks and benefits of the emergency use of the ID NOW COVID-19.

The ID NOW COVID-19 is authorized for use on respiratory specimens collected from individuals who are suspected of COVID-19 by their healthcare provider.

All patients whose specimens are tested with this assay will receive the Fact Sheet for Patients: ID NOW COVID-19.

What are the symptoms of COVID-19?

Many patients with confirmed COVID-19 have developed fever and/or symptoms of acute respiratory illness (e.g., cough, difficulty breathing). The current information available to characterize the spectrum of clinical illness associated with COVID-19 suggests that symptoms include cough, shortness of breath or dyspnea, fever, chills, myalgias, headache, sore throat or new loss of taste or smell. Based on what is known about the virus that causes COVID-19, signs and symptoms may appear any time from 2 to 14 days after exposure to the virus. Based on preliminary data, the median incubation period is approximately 5 days, but may range 2-14 days.

Public health officials have identified cases of COVID-19 infection throughout the world, including the United States, which may pose risks for public health. Please check the CDC webpage for the most up to date information.

What do I need to know about COVID-19 testing?

Current information on COVID-19 for healthcare providers is available at CDC's webpage, *Information for Healthcare Professionals* (see links provided in "Where can I go for updates and more information" section).

- The ID NOW COVID-19 can be used to test direct nasal, nasopharyngeal or throat swabs.
- The ID NOW COVID-19 should be ordered for the detection of COVID-19 in individuals who are suspected of COVID-19 by their healthcare provider.
- The ID NOW COVID-19 is authorized for use in laboratories certified under the Clinical Laboratory Improvement Amendments of 1988 (CLIA), 42 U.S.C. §263a, to perform high and moderate complexity tests.
- The ID NOW COVID-19 Test is authorized to be distributed and used in patient care settings using the ID NOW Instrument outside of the clinical laboratory environment.

This test is to be performed only using respiratory specimens collected from individuals who are suspected of COVID-19 by their healthcare provider.

Specimens should be collected with appropriate infection control precautions. Current guidance for COVID-19 infection control precautions are available at the CDC's website (see links provided in "Where can I go for updates and more information" section).

Use appropriate personal protective equipment when collecting and handling specimens from individuals suspected of having COVID-19 as outlined in the CDC Interim Laboratory Biosafety Guidelines for Handling and Processing Specimens Associated with Coronavirus Disease 2019 (COVID-19). For additional information, refer to CDC Interim Guidelines for Collecting, Handling, and Testing Clinical Specimens from Persons Under Investigation (PUIs) for Coronavirus Disease 2019 (COVID-19) (see links provided in "Where can I go for updates and more information" section).

What does it mean if the specimen tests positive for the virus that causes COVID-19?

A positive test result for COVID-19 indicates that RNA from SARS-CoV-2 was detected, and the patient is infected with the virus and presumed to be contagious. Laboratory test results should always be considered in the context of clinical observations and epidemiological data in making a final diagnosis and patient management decisions. Patient management should follow current CDC guidelines.

The ID NOW COVID-19 has been designed to minimize the likelihood of false positive test results. However, in the event of a false positive result, risks to patients could include the following: a recommendation for isolation of the patient, monitoring of household or other close contacts for symptoms, patient isolation that might limit contact with family or friends and may increase contact with other potentially COVID-19 patients, limits in the ability to work, the delayed diagnosis and treatment for the true infection causing the symptoms, unnecessary prescription of a treatment or therapy, or other unintended adverse effects.

All laboratories and healthcare providers in patient care settings using this test must follow the standard testing and reporting guidelines according to their appropriate public health authorities.



FACT SHEET FOR HEALTHCARE PROVIDERS

ID NOW COVID-19 - Abbott Diagnostics Scarborough, Inc.

Updated: June 1, 2020

Coronavirus
Disease 2019
(COVID-19)

What does it mean if the specimen tests negative for the virus that causes COVID-19?

A negative test result for this test means that SARS-CoV-2 RNA was not present in the specimen above the limit of detection. However, a negative result does not rule out COVID-19 and should not be used as the sole basis for treatment or patient management decisions. A negative result does not exclude the possibility of COVID-19. Negative results should be treated as presumptive and, if inconsistent with clinical signs and symptoms or necessary for patient management, should be tested with an alternative molecular assay.

When diagnostic testing is negative, the possibility of a false negative result should be considered in the context of a patient's recent exposures and the presence of clinical signs and symptoms consistent with COVID-19. The possibility of a false negative result should especially be considered if the patient's recent exposures or clinical presentation indicate that COVID-19 is likely, and diagnostic tests for other causes of illness (e.g., other respiratory illness) are negative. If COVID-19 is still suspected based on exposure history together with other clinical findings, retesting with an alternative method should be considered by healthcare providers in consultation with public health authorities.

Risks to a patient of a false negative include: delayed or lack of supportive treatment, lack of monitoring of infected individuals and their household or other close contacts for symptoms resulting in increased risk of spread of COVID-19 within the community, or other unintended adverse events.

What is an EUA?

The United States FDA has made this test available under an emergency access mechanism called an Emergency Use Authorization (EUA). The EUA is supported by the Secretary of Health and Human Service's (HHS's) declaration that circumstances exist to justify the emergency use of in vitro diagnostics (IVDs) for the detection and/or diagnosis of the virus that causes COVID-19.

An IVD made available under an EUA has not undergone the same type of review as an FDA-approved or cleared IVD. FDA may issue an EUA when certain criteria are met, which includes that there are no adequate, approved, available alternatives, and based on the totality of scientific evidence available, it is reasonable to believe that this IVD may be effective in the detection of the virus that causes COVID-19.

The EUA for this test is in effect for the duration of the COVID-19 declaration justifying emergency use of IVDs, unless terminated or revoked (after which the test may no longer be used).

Where can I go for updates and more information?

CDC webpages:

General: https://www.cdc.gov/COVID19

Healthcare Professionals:

https://www.cdc.gov/coronavirus/2019-nCoV/guidance-hcp.html

Information for Laboratories:

https://www.cdc.gov/coronavirus/2019-nCoV/quidance-

laboratories.html

Laboratory Biosafety: https://www.cdc.gov/coronavirus/2019-

nCoV/lab-biosafety-guidelines.html

Isolation Precautions in Healthcare Settings:

https://www.cdc.gov/coronavirus/2019-ncov/infection-

control/control-recommendations.html

Specimen Collection: https://www.cdc.gov/coronavirus/2019-

nCoV/guidelines-clinical-specimens.html

Infection Control: https://www.cdc.gov/coronavirus/2019-

ncov/infection-control/index.html

FDA webpages:

General: www.fda.gov/novelcoronavirus

EUAs:(includes links to patient fact sheet and manufacturer's instructions) https://www.fda.gov/medical-devices/emergency-use-authorizations

Abbott Diagnostics Scarborough, Inc.:

Abbott Diagnostics Scarborough, Inc. 10 Southgate Road Scarborough, ME, USA, 04074

Customer Support:

+1 855 731-2288

ts.scr@abbott.com

Technical Support:

+1 855 731-2288

ts.scr@abbott.com

<u>Website:</u>

https://www.alere.com/en/home/product-details/id-now-COVID-19.html

TB000039 Rev. 5

© 2020 Abbott. All rights reserved. All trademarks referenced are trademarks of either the Abbott group of companies or their respective owners.