

TaqMan® Fast Advanced Master Mix on the Bio-Rad CFX96™ Real-Time PCR System

Introduction


TaqMan® Fast Advanced Master Mix has been designed to match or exceed the performance of standard master mixes, delivering shorter run times (<40 minutes) with results equal to or better than what you achieve today.

Highlighted here is the performance of TaqMan® Fast Advanced Master Mix on the Bio-Rad CFX96™ system with TaqMan® Gene Expression Assays. The results demonstrate the superior performance obtained using TaqMan® Fast Advanced Master Mix compared to that obtained using Bio-Rad's recommended probe-based reagent on the Bio-Rad CFX96™ system.

Benefits of TagMan® Fast Advanced Master Mix: not just fast cycling (<40 min)

- Best-in-class performance—superior sensitivity, accuracy, dynamic range, and specificity compared to standard mixes in standard mode
- Enhanced benchtop stability for high-throughput handling and convenience—stable at room temperature for up to 72 hours in preassembled reactions
- Optimized for multiplexing—validated for duplexing with exogenous and endogenous internal positive control assays
- Seamlessly transitions into experiments—validated with Applied Biosystems® TaqMan® Assays for gene expression and microRNAs

A. Standard assay (amplicon <30% GC)



B. GC-rich assay (amplicon >70% GC)




Figure 1. Comparison data for TaqMan® Fast Advanced Master Mix and Bio-Rad's recommended probe-based reagent on the Bio-Rad CFX96™ system. PCR reactions were performed on the Bio-Rad CFX96™ system using a dilution series containing 100 ng to 0.01 ng of template cDNA. The amplification plots demonstrate the superiority of TaqMan® Fast Advanced Master Mix over Bio-Rad's recommended probe-based reagent. Each reagent was used according to the manufacturers' respective recommended protocols.

Run the experiment

1. Prepare the PCR reaction mix.

- 1. Thoroughly mix TagMan® Fast Advanced Master Mix.
- 2. Thaw frozen samples and frozen TagMan® Assays on ice. Resuspend by vortexing, then briefly centrifuge.
- 3. Calculate the total volume required for each component: volume for 1 reaction x total number of reactions.
- 4. Mix gently. Do not vortex. Centrifuge briefly and then prepare the PCR reaction plate.

	Volume (µL) for 1 reaction			
Component	384-well plate	96-well plate	Final concentration	
TaqMan® Fast Advanced Master Mix (2X)*	5.0	10.0	1X	
TaqMan® Assay primer/probe (20X)	0.5	1.0	1X	
cDNA template	1.0	2.0	0.001-100 ng/well	
Nuclease-free water	3.5	7.0		
Total volume per reaction	10.0	20.0		
*ROX" dye is included in the TaqMan® Fast Advanced Master Mix. The Bio-Rad CFX96" Real-Time PCR System can detect this dye, but it will not be used for fluorescence				

normalization in the Bio-Rad CFX96™ system software.

2. Set up the run method.

See your instrument's user manual for detailed instructions on how to configure the run method.

Bio-Rad CFX96™ System	UNG activation	Polymerase activation	PCR (40 cycles)			
	Hold	Hold	Denature	Anneal/extend		
Temperature	50°C	95°C	95°C	60°C		
Time (min:sec)	02:00	00:20	00:03	00:30		
* Before setup, check your primer annealing temperature. If the primer T_m is <60°C, we recommend using a 3-step protocol.						

3. Run the PCR reaction plate.

Load the reaction plate into the instrument and start the run. See your instrument's user manual for detailed instructions on how to load and run the plate.

4. Analyze the results.

Data analysis varies depending on the instrument. See the TagMan® Fast Advanced Master Mix Protocol (PN 4444605) and your instrument's user manual for detailed instructions on how to analyze the data.

ORDERING INFORMATION

Product	Size	Quantity	Number of 20 µL reactions	Cat. No.
TaqMan® Fast Advanced Master Mix	Mini-Pack	1 x 1 mL	100	4444556
	1-Pack	1 x 5 mL	500	4444557
	2-Pack	2 x 5 mL	1,000	4444963
	5-Pack	5 x 5 mL	2,500	4444964
	10-Pack	10 x 5 mL	5,000	4444965
	Bulk-Pack	1 x 50 mL	5,000	4444558

For safety and biohazard guidelines, refer to the MSDS and follow the handling instructions. Work only in a suitably equipped laboratory space (including, without limitation, proper ventilation, electrical installation, hazardous waste disposal) and wear appropriate protective eyewear, clothing, and gloves.

This document shows (1) simplified procedures for using TaqMan® Fast Advanced Master Mix on the Bio-Rad CFX96™ Real-Time PCR System, and (2) comparison data for TaqMan® Fast Advanced Master Mix and Bio-Rad's recommended probe-based reagent on the Bio-Rad CFX96™ Real-Time PCR System. The TaqMan® Fast Advanced Master Mix Protocol (Part Number 4444605) provides detailed instructions.

Life Technologies offers a breadth of products DNA | RNA | PROTEIN | CELL CULTURE | INSTRUMENTS

NOTICE TO PURCHASER: Please refer to the TaqMan® Fast Advanced Master Mix Protocol (PN 4444605) and user's manual FOR LIMITED LABEL LICENSE OR DISCLAIMER INFORMATION.

For Research Use Only. Not intended for any animal or human therapeutic or diagnostic use.

© 2011 Life Technologies Corporation. All rights reserved. The trademarks mentioned herein are the property of Life Technologies Corporation or their respective owners. TaqMan is a registered trademark of Roche Molecular Systems, Inc. CFX96 is a trademark of Bio-Rad Laboratories, Inc., and no sponsorship, endorsement, or affiliation is implied herein. Printed in the USA. C031415 0711

