## *fisher*brand

# Digital dry baths/block heaters

Versatile digital dry baths/block heaters to meet your laboratory needs

Fisherbrand<sup>™</sup> Isotemp<sup>™</sup> reliable digital dry baths/block heaters offer outstanding temperature uniformity and stability with a wide range of blocks to accommodate various tubes.

#### Applications

- Sample preparation
- Enzyme preservation
- Enzyme-substrate reactions
- DNA amplification
- Electrophoresis gel degeneration
- Serum coagulation
- Heating or thawing tubes and plates

#### Benefits

- Digital time and temperature display
- Temperature range: ambient +5 °C - 130 °C
- Built-in temperature sensing probe for outstanding accuracy and control
- Precise temperature control with PID circuit
- Temperature calibration offsets the temperature to desired value
- Interchangeable aluminum alloy blocks provide versatility, easy cleaning and disinfecting
- Range of configurations hold 1, 2 or 4 interchangeable modular blocks which can hold a variety of tube sizes
- Powder-coated steel body construction ensures durability









#### Specifications and ordering information

	Catalog Number						
	88860021	88860022	88860023				
Number of Blocks	1	2	4				
Temperature Range	Ambient +5 °C-130 °C						
Controller Type	PID digital						
Temperature Control Accuracy	At 37 °C $\leq \pm 0.5$ °C						
Temperature Uniformity	$\leq \pm 1  {}^{\circ}\text{C}$						
Timing Range	0-99:59 min or continuous						
Heating Up Time	$\leq$ 20 minutes (30 °C to 130 °C) $\leq$ 25 minutes (30 °C to 130 °C)						
Operating Temperature	10°C ~ 30 °C						
Relative Humidity Tolerance	≤ 80%						
Dimensions L x W x H	288×200×100 mm 11.3×7.9×3.9 in	318×200×100 mm 12.5×7.9×3.9 in	450×200×100 mm 17.7×7.9×3.9 in				
Weight	2.9 kg 6.39 lbs.	3.3 kg 7.28 lbs.	4.7 kg 10.36 lbs.				
Power	100-120V~50/60Hz						
Shipment Includes	Dry bath, US style plug, block lifter						
Certification	CE, cULus, RoHS						
Warranty	2 years						

#### Aluminum block accessories

	88860101	46 x ø6 mm flat bottom, 31mm depth		88860112	Mixed block 32 x ø6 mm + 21 x ø10mm, 31mm depth
	88860102	28 x ø10 mm flat bottom, 31mm depth		88860113	Mixed block 18 x 1.5 ml + 10 x 2.0 ml, 31mm depth
	88860103	28 x 1.5 ml conical bottom, 31mm depth		88860114	Mixed block 3 x ø25 mm + 12 x ø12~13 mm + 6 x ø6 mm, 31mm depth
	88860104	28 x 2.0 ml conical bottom, 31mm depth		88860115	Mixed block 30 x 0.5 ml + 20 x 0.2 ml, 31mm depth
AND A	88860105	24 x ø13 mm flat bottom, 31mm depth		88860116	Flat bottom, 15 x 15 ml, 115mm depth
	88860106	15 x ø16 mm flat bottom, 31mm depth	4	88860117	Flat bottom, 4 x 50 ml, 115mm depth
	88860107	12 x ø18 mm flat bottom, 31mm depth		88860118	Conical bottom, 15 x 15 ml aluminum block, 115mm depth
	88860108	8 x ø20 mm flat bottom, 31mm depth	1	88860119	Conical bottom, 4 x 50 ml aluminum block, 115mm depth
	88860109	6 x ø25 mm flat bottom, 31mm depth		88860120	1 x 96-well 0.2 ml non-skirted PCR plate, 11mm depth
-	88860110	40 x 0.5 ml conical bottom, 31mm depth		88860121	1 x 96-well 0.2 ml, half or full skirted PCR plate, 11mm depth
-	88860111	1 x 96-well ELISA			

### Find out more at fishersci.com

© 2017 Thermo Fisher Scientific Inc. All rights reserved. Trademarks used are owned as indicated at fishersci.com/trademarks.

#### In the United States:

For customer service, call 1-800-766-7000 To fax an order, use 1-800-926-1166 To order online: fishersci.com

#### In Canada:

For customer service, call 1-800-234-7437 To fax an order, use 1-800-463-2996 To order online: fishersci.ca

