



Handling protection

ULTRANE 500

Grip and skin protection for oily environments.



GRIP & PROOF
TECHNOLOGY

SPECIFIC ADVANTAGES



Durability

- Color adapted to dirty environments for a prolonged durability.
- Excellent abrasion resistance due to the nitrile coating



Productivity

- Grip and Proof coating ensures an excellent grip in oily environment. It also reduces muscle strain and boost productivity



Skin protection

- Oilproof, it repels oil penetration and reduce dermatitis
- Free of harmful substances: DMF Free



Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting



Washability

- Washable 3 times at 40° without any alteration on performances* to extend lifespan, reduce costs and waste



Additional benefits

Available in vending machine packaging

INDUSTRIES

- Automotive/mechanical industry
- Mechanical industry
- Other industries
- Glass industry
- Agriculture sector

APPLICATIONS

- Maintenance in wet environments
- Handling glass sheets
- Re-entry tasks
- Cutting and stamping metal
- Maintenance in wet environments (water, oil, greases, hydrocarbons)
- Handling and sorting small, sharp parts
- Handling oily mechanical parts
- Handling sheet metal
- Machining parts using cutting oil

EN388 4121A	EN407 X1XXXX	ANSI CUT A1 CUT
 GR ISO 18889	CAT.3 0075	ISO 13997: 5 N
DEXTERITY EN 420: 5/5	 CONFIDENCE IN TEXTILES STANDARD 100 CQ 979/2 IFTH Tested for harmful substances. www.oeko-tex.com/standard100	

Size	Packaging	Fisher Scientific Cat. Nos.	MAPA Cat. Nos.
6	Pair	19249815	500416
7	Pair	19249816	500417
8	Pair	19249817	500418
9	Pair	19249818	500419
10	Pair	19249819	500410
11	Pair	19249820	500411

Find it at fishersci.com and fishersci.ca




Handling protection

ULTRANE 500

LEGENDS

EN388 MECHANICAL HAZARDS




PERFORMANCE LEVELS (X = NOT TESTED)

4 1 2 1 A
 0-4 0-5 0-4 0-4 A-F P

Abrasion resistance
 Blade cut resistance
 Tear resistance
 Puncture resistance
 Cut resistance according to ISO 13997
 Impact protection (optional)

EN407 THERMAL RISKS (HEAT AND FIRE)




PERFORMANCE LEVELS (X = NOT TESTED)

X 1 X X X X
 0-4 0-4 0-4 0-4 0-4 0-4


Limited flame spread
 Contact heat resistance
 Convective heat resistance
 Radiant heat resistant
 Small splashes of molten metal
 Resistance to large quantities of molten metal

PROTECTION FROM PESTICIDES
 GR: Re-entry tasks



ISO 18889

ANSI CUT CUT RESISTANCE
 A1 ≥ 200 G



ALIMENTARY
 US (FDA)



PRODUCT DETAILS

Interior finish	Seamless textile support
Gauge	13
Exterior finish	Ventilated back
Material	Nitrile GRIP&PROOF coating
Cuff characteristic	Knitted Cuff
Colour.s	Black
Size	6 7 8 9 10 11
Surface resistance according to EN1149-1 (Value in palm area at 25% relative humidity)	1.1E+10 Ω
Vertical resistance according to EN1149-2 (Value in palm area at 25% relative humidity)	4.4E+11 Ω

LOGISTIC DETAILS

Packaging	1 pair/bag 12 pairs/bag 96 pairs/carton
-----------	---

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/09/18/1953
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0075 | CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE

Distributed by Fisher Scientific. Contact us today:

In the United States
 Order online: fishersci.com
 Call customer service: 1-800-766-7000

In Canada
 Order online: fishersci.ca
 Call customer service: 1-800-234-7437

