


Chromatography: Sample Preparation Workflow



Chemicals

From sample preparation to separation, Fisher Chemical Optima high-purity solvents, additives, and solvent blends have set the standard of excellence for consistent, reproducible performance for all your chromatography applications.

Solvents and Solvent Blends	Cat. No.
Acetonitrile, Optima Grade, for HPLC and GC, 4L	A996-4
Methylene Chloride, Optima Grade, for HPLC/GC, 4L	D151-4
Hexanes, Optima Grade, for HPLC/GC, 4L	H303-4
Chloroform, Amylene-Stabilized, Optima Grade, for HPLC/GC, 4L	C297-4
Acetone, Optima Grade, for HPLC/GC, 4L	A929-4
Ethyl Ether, Stabilized, Anhydrous, HPLC Grade, 4L	E198-4

Additives and Salts	Cat. No.
Magnesium Sulfate, Anhydrous, Certified, 3kg	M65-3
Sodium Sulfate, Anhydrous, Certified ACS, 1kg	S415-1
Sodium Chloride, Certified ACS, 3kg	S271-3
Sodium Acetate Trihydrate, Certified ACS, 3kg	S209-3
Tribasic Sodium Citrate Dihydrate, Certified, 3kg	S279-3
Dibasic Sodium Citrate Sesquihydrate, Pure, 250g	AC250242500
Formic Acid, Optima LC-MS Grade, 10 x 1mL Ampules	A11710X1-AMP
Acetic Acid, Optima LC-MS Grade, 10 x 1mL Ampules	A11310X1-AMP

Visit the Workflows section of fishersci.com/fisherchemical or fishersci.ca/fisherchemical to shop more chromatography sample prep products.

SPE Cartridges, Digestion Kits, SPE Plates, and Syringe Filters

Choose from a broad range of solid-phase extraction (SPE) consumables and syringe filters to solve your sample preparation challenges, including sample and throughput constraints.

Extraction

Thermo Scientific HyperSep Cartridges deliver greater reproducibility and recovery.

Description	Cat. No.
PEP Cartridges, 30mg, 3mL	03-150-634
SCX Cartridges, 30mg, 3mL	03-150-640
SAX Cartridges, 30mg, 3mL	03-150-646

Digestion

Get fast and simple protein digestion with Thermo Scientific SMART Digest Kits.

Description	Cat. No.
Trypsin Kit	03-150-404
Trypsin Kit, Magnetic Bulk Resin	03-375-364

Concentration

Thermo Scientific SOLA μ Plates help you get clean, robust extractions with low sample and solvent volumes.

Description	Cat. No.
HRP 96-Well Plates	60-209-001
SCX 96-Well Plates	60-209-002
SAX 96-Well Plates	60-209-003
10mg HRP 96-Well Plates	03-150-394
10mg SCX 96-Well Plates	03-150-395
10mg SAX 96-Well Plates	03-150-396

Clean up

Thermo Scientific Titan3 Syringe Filters prevent sample leakage, increasing confidence in your results.


Description	Cat. No.
Filters with Pre-Filter, 30mm, 0.2 μ m	14-823-287
Filters with Pre-Filter, 30mm, 0.45 μ m	14-823-296
Filters, 30mm, 0.45 μ m	03-050-492
Filters, 17mm, 0.2 μ m	03-050-371
Filters, 17mm, 0.45 μ m	14-823-291

Visit fishersci.com/thermochrom or fishersci.ca/thermochrom to shop more chromatography sample prep products.

Trademarks of Thermo Fisher Scientific:

Acclaim, Accucore, Chromacol, Chromplete, Fisher Chemical, GC Resolv, HyperSep, Hypersil GOLD, LinerGOLD, Optima, SMART Digest, SOLA μ , SureStop, Synchronis, Target2, Thermo Scientific, Titan3, TRACE, TraceGOLD, VANQUISH, Verify, WebSeal

Chromatography: HPLC Reverse-Phase Workflow



Chemicals

Fisher Chemical Optima HPLC solvents and additives are manufactured in facilities with an ISO 9001:2015-certified quality system to ensure optimum quality and product uniformity for your HPLC reverse-phase applications.

Solvents and Solvent Blends	Cat. No.
Acetonitrile, Optima Grade, for HPLC and GC, 4L	A996-4
Methanol, Optima Grade, for HPLC, 4L	A454-4
Water, Optima Grade, for HPLC, 4L	W7-4
Water with 0.1% TFA, for HPLC, 4L	HB513-4
Water with 0.1% FA, for HPLC, 4L	HB523-4
Isopropanol, Optima Grade, for HPLC, 4L	A464-4

Additives	Cat. No.
Acetic Acid, Optima Grade, LC/MS, 50mL	A113-50
TFA, Optima Grade, LC/MS Grade, 10mL	A116-10X1AMP
o-Phosphoric Acid, HPLC Grade, 500mL	A260-500
Ammonium Hydroxide, Optima Grade, 250mL	A470-250
Triethylamine (TEA), HPLC, 100mL	O4884-100
Heptane Sulfonic Acid, Na Salt, HPLC	O313-100
1-Octane Sulfonic Acid, Sodium Salt	O0028-100

Visit the Workflows section of fishersci.com/fisherchemical or fishersci.ca/fisherchemical to shop more HPLC products.

Syringe Filters, Cartridges, Plates, Vials, and Columns

Let innovative Thermo Scientific technology remove uncertainty from your results.

Sample Preparation

Clean Up

Thermo Scientific Titan3 Syringe Filters can prevent sample leakage, increasing confidence in your results.

Description	Cat. No.
Filters with Pre-Filter, 30mm, 0.2µm	14-823-287
Filters with Pre-Filter, 30mm, 0.45µm	14-823-296
Filters, 30mm, 0.45µm	03-050-492
Filters, 17mm, 0.2µm	03-050-371
Filters, 17mm, 0.45µm	14-823-291

Extract

Thermo Scientific HyperSep Cartridges deliver greater reproducibility and recovery.

Description	Cat. No.
Retain PEP Cartridges, 30mg, 3mL	03-150-634
Retain SCX Cartridges, 30mg, 3mL	03-150-640
Retain SAX Cartridges, 30mg, 3mL	03-150-646

Concentrate

Get clean, highly reproducible sample extracts with lower elution volumes using Thermo Scientific SOLAµ Solid-Phase Extraction (SPE) Plates.

Description	Cat. No.
HRP 96-Well Plates	60-209-001
SCX 96-Well Plates	60-209-002
SAX 96-Well Plates	60-209-003

Sample Handling

Choose from a range of Thermo Scientific microplates and vials that produce precise results and unmatched consistency.

WebSeal Microplates	Cat. No.
96-Well Non-Coated Plastic Microplates	03-252-401
SureStop Vials and Kits	Cat. No.
Autosampler Kits, Clear, 9mm	03-170-331
Vials, Clear, 2mL	03-376-601
Vials, Amber, 2mL	03-376-602
Vials, Clear, 2mL, PTFE/Rubber Septa	03-376-604
Vials, Clear, 2mL, PTFE/Silicone Septa	03-376-606
Vials, Amber, 2mL, PTFE/Silicone Septa	03-377-300
Vials, Clear, 200µL Fused Insert, PTFE/Silicone Septa	03-060-050
Vials, Clear Glass, 1.7mL, PTFE/Silicone Septa	03-060-052


Visit fishersci.com/thermochrom or fishersci.ca/thermochrom to see all HPLC reverse-phase products.

Separation

Choose from a range of columns that optimize separations and provide enhanced retention or changes in elution order.

Hypersil GOLD Columns	Cat. No.
C18 HPLC Column, 3µm, 150 x 4.6mm	25003154630
C18 HPLC Column, 1.9µm, 50 x 2.1mm	25002052130
Vanquish UHPLC Column, 1.9µm, 100 x 2.1mm	03-051-471
Phenyl HPLC Column, 3µm, 150 x 4.6mm	03-051-191
aQ Polar Endcapped LC/MS Column, 1.9µm, 50 x 4.6mm	03-170-552
Acclaim Columns	Cat. No.
C18 HPLC and LC/MS Column, 2.2 – 5µm, 2.1 x 100mm	DX068982
Polar Advantage II LC/MS and RSLC Column, 2.2µm, 2.1 x 100mm	DX068990
C30 LC/MS Column, 5µm, 4.6 x 250mm	DX075718
Accucore Columns	Cat. No.
HPLC and RP/MS Column, 2.6µm, 2.1 x 100mm	17-626-102130
C18 HPLC/UHPLC Column, LC/MS, 2.6µm, 2.1 x 100mm	17-126-102130
aQ Polar Endcapped HPLC Column, 2.6µm, 2.1 x 100mm	17-326-102130
Biphenyl HPLC/UHPLC Column, 2.6µm, 2.1 x 100mm	03-251-529

Chromatography: HPLC Normal-Phase Workflow



Chemicals

Fisher Chemical Optima HPLC solvents and additives are manufactured in facilities with an ISO 9001:2015-certified quality system to ensure optimum quality and product uniformity for your HPLC normal-phase applications.

Solvents and Solvent Blends	Cat. No.
n-Hexane, 95%, Optima Grade, for HPLC, GC/MS, 4L	H306-4
Hexanes, Optima Grade, for HPLC, GC/MS, 4L	H303-4
Chloroform, Amylene-Stabilized, Optima Grade, for HPLC/GC, 4L	C297-4
n-Heptane, 99%, Optima Grade, for HPLC/GC, 4L	E360-4
2-Propanol, Chromplete, HPLC/GC Grade, ACS, USP, 4L	T001044000
Ethyl Acetate, Optima Grade, for HPLC/GC, 4L	E196-4
Tetrahydrofuran, Optima Grade, 4L	T427-4
Methyl tert-Butyl Ether, HPLC Grade, 4L	E127-4
Methylene Chloride, Optima Grade, for HPLC, GC/MS, 4L	D151-4
Ethyl Ether, Stabilized, Anhydrous, HPLC Grade, 4L	E198-4

Additives	Cat. No.
Formic Acid, 99.0+%, Optima LC/MS Grade, 50mL	A11750
Ammonium Acetate, HPLC Grade, 500g	A639500
Triethylamine (TEA), HPLC Grade, 500mL	O4884500
Ammonium Hydroxide, Optima Grade, 250mL	A470250
Acetic Acid, Optima LC/MS Grade, 50mL	A11350
Ammonium Formate, Optima LC/MS Grade, 50g	A11550

Visit the Workflows section of fishersci.com/fisherchemical or fishersci.ca/fisherchemical to shop more HPLC products.

Syringe Filters, Cartridges, Plates, Vials, and Columns

Let innovative Thermo Scientific technology remove uncertainty from your results.

Sample Preparation

Clean Up

Thermo Scientific Titan3 Syringe Filters can prevent sample leakage, increasing confidence in your results.

Description	Cat. No.
Filters with Pre-Filter, 30mm, 0.2µm	14-823-287
Filters with Pre-Filter, 30mm, 0.45µm	14-823-296
Filters, 30mm, 0.45µm	03-050-492
Filters, 17mm, 0.2µm	03-050-371
Filters, 17mm, 0.45µm	14-823-291

Extract

Thermo Scientific HyperSep Cartridges deliver greater reproducibility and recovery.

Description	Cat. No.
Retain PEP Cartridges, 30mg, 3mL	03-150-634
Retain SCX Cartridges, 30mg, 3mL	03-150-640
Retain SAX Cartridges, 30mg, 3mL	03-150-646

Concentrate

Get clean, highly reproducible sample extracts with lower elution volumes using Thermo Scientific SOLAµ Solid-Phase Extraction (SPE) Plates.

Description	Cat. No.
HRP 96-Well Plates	60-209-001
SCX 96-Well Plates	60-209-002
SAX 96-Well Plates	60-209-003

Sample Handling

Choose from a range of Thermo Scientific microplates and vials that produce precise results and unmatched consistency.

SureStop Vials and Kits	Cat. No.
Autosampler Kits, Clear, 9mm	03-170-331
Vials, Clear, 2mL	03-376-601
Vials, Amber, 2mL	03-376-602
Vials, Clear, 2mL, PTFE/Rubber Septa	03-376-604
Vials, Clear, 2mL, PTFE/Silicone Septa	03-376-606
Vials, Amber, 2mL, PTFE/Silicone Septa	03-377-300
Vials, Clear, 200µL Fused Insert, PTFE/Silicone Septa	03-060-050
Vials, Clear Glass, 1.7mL, PTFE/Silicone Septa	03-060-052


Visit fishersci.com/thermochrom or fishersci.ca/thermochrom to see all HPLC normal-phase products.

Separation

Choose from a range of bonded and non-bonded normal-phase columns that are ideal for the retention and separation of lipophilic compounds.

Hypersil GOLD Columns	Cat. No.
Hypersil GOLD LC Column, 5µm, 4.6 x 250mm	25-105-254030
Hypersil GOLD LC Column, 1.9µm, 2.1 x 100mm	25-102-102130
Hypersil GOLD PEI HILIC LC Column, 5µm, 4.6 x 250mm	26-505-254630
Hypersil GOLD PEI HILIC LC Column, 3µm, 2.1 x 150mm	26-503-152130
Accucore 150 Amide HILIC LC Column, 2.6µm, 2.1 x 150mm	03-452-150
Accucore Urea HILIC LC Column, 2.6µm, 2.1 x 100mm	03-452-125
Accucore HILIC LC Column, 2.6µm, 2.1 x 150mm	17-526-152130
Acclaim HILIC-10 LC Column, 3µm, 4.6 x 150mm	DX074257
Acclaim Mixed-Mode HILIC-1 LC Column, 5µm, 4.6 x 150mm	DX066843
Acclaim Mixed-Mode HILIC-1 LC Column, 5µm, 4.6 x 250mm	DX066844
Synchronis HILIC LC Column, 1.7µm, 2.1 x 100mm	03-050-348
Synchronis Silica LC Column, 5µm, 4.6 x 250mm	97-005-254630

Chromatography: GC Workflow



Chemicals

From sample preparation to separation, Fisher Chemical GC Resolv solvents and solvent blends have set the standard of excellence for consistent, reproducible GC performance.

Solvents and Solvent Blends	Cat. No.
N,N-Dimethylformamide, DMF, GC Headspace Grade, 1L	D133-1
Dimethyl Sulfoxide, DMSO, GC Headspace Grade, 1L	D139-1
N,N-Dimethylacetamide, DMAC, GC Headspace Grade, 1L	D160-1
1-Methyl-2-Pyrrolidone, NMP, GC Headspace Grade, 1L	N140-1
Water, Chromplete, for HPLC/GC, Spectrometry, 4L	T001034000
Methanol, Purge & Trap, 1L	A453-1
Acetonitrile, Chromplete, HPLC/GC Grade, ACS, USP, 4L	T001014000
Methylene Chloride, Optima Grade, for HPLC/GC, 4L	D151-4

Solvents and Solvent Blends	Cat. No.
Hexanes, Optima Grade, for HPLC/GC, 4L	H303-4
Chloroform, Amylene-Stabilized, Optima Grade, for HPLC/GC, 4L	C297-4
Acetone, Optima Grade, for HPLC/GC, 4L	A929-4
Ethyl Ether, Stabilized, Anhydrous, for HPLC, 4L	E198-4

Visit the Workflows section of fishersci.com/fisherchemical or fishersci.ca/fisherchemical to see more GC products.

Syringe Filters, Cartridges, Vials, and Columns

Choose these GC solutions for your most complex separations. Pharmaceutical, industrial, food, environmental, and other fields rely on these products to improve processes and protect people and the environment from harmful contaminants.

Sample Preparation

Clean Up

Ensure cleaner sample extracts with robust Thermo Scientific Target2 GMF (glass microfiber) Syringe Filters.

Description	Cat. No.
Syringe Filters, 30mm, 3.1µm, 100/pk	03-376-224

Extract

Thermo Scientific HyperSep Cartridges deliver greater reproducibility and recovery.

Description	Cat. No.
Dispersive Extraction Products, 50mL	03-152-613
Dispersive Clean-Up Products, 15mL	03-150-309
C18 Cartridges, 75mL	03-251-292
Verify AX Cartridges, 6mL	03-251-313
Aminopropyl Cartridges, 3mL	03-251-169
C18 Cartridges, 75mL	03-251-292
Verify CX Cartridges, 3mL	60-108-777

Sample Handling

Save time during sample preparation and reduce the risk of contamination using Thermo Scientific vials, available with flat or round bottoms and screw-thread or crimp-cap tops.

Description	Cat. No.
Autosampler Vial Kits, Clear, 9mm, 100/Pack	03-170-331
Chromacol GOLD-Grade Inert Vials, 11mm, Clear, 2mL	03-251-445
Crimp Caps, Aluminum, 11mm, Red PTFE/White Silicone Septa, 100/Pack	06-406-19D
Headspace Vials, 18mm, Clear Glass	14-824-365
Screw Caps, 18mm, Blue Silicone/Natural PTFE Septa	03-378-621
Vials, 9mm, Amber Glass	03-377F
Screw Caps, 9mm, Blue, Red PTFE/White Silicone Septa	03-376-481
Vials, 9mm, Amber, with 300µL Fused Insert	13-622-257
Screw Caps, 9mm, Blue, Clear PTFE/Blue Silicone Septa	60180516
Vials, 9mm, Clear, with 200µL Fused Insert	03-060-058

Separation

Thermo Scientific TraceGOLD Fast GC Columns are shorter and smaller than conventional GC columns for faster analysis with the same separation.

Description	Cat. No.
TG-5SILMS Guard Column with SafeGuard, 0.25µm, 0.25mm x 30m	03-155-047
TG-OCP I Column, 0.25µm, 0.25mm x 30m	26078-1420
TG-5SiIMS Column, 0.25µm, 0.25mm x 30m	26096-1420
TG-PAH Column, 0.25µm, 0.25mm x 30m	26055-0470
TG-XLBMS Column, 0.25µm, 0.25mm x 30m	26079-1420
TR-FAME Column, 0.2µm, 0.25mm x 100m	03-052-622
TRACE Columns for Drugs of Abuse, 0.25mm x 15m	26AF130P
LinerGOLD Splitless Straight GC Liner, Quartz Wool, 4 x 78.5mm	03-151-660
LinerGOLD Splitless Straight GC Liner, No Packing, 5 x 105mm	45350033
LinerGOLD GC Liner, PTV Baffle (Siltek), 2 x 120mm	45-3T2-120

In the United States

Order online: fishersci.com
 Fax an order: 1-800-926-1166
 Call customer service: 1-800-766-7000

In Canada

Order online: fishersci.ca
 Fax an order: 1-800-463-2996
 Call customer service: 1-800-234-7437

