



HUMIDITY TEST CHAMBERS

Available 120V/60Hz

- Homogeneous climate even when fully loaded ensured by APT.line™ preheating chamber technology. 30% more load per shelf than conventional chambers
- Temperature range: 0 °C to +70 °C, Temperatures down to 28°C below ambient possible
- Exceptionally energy-saving due to BINDERs Peltier technology
- Exceptionally low noise level due to inside ventilator positioning
- Environmental-friendly without refrigerants

Serie KBF-S ECO

with Peltier-Technology!


The most energy-efficient constant climate chamber in its class

SAFE




Homogeneous climate due to APT.line™ double-sided airflow ensures full coverage of the ICH Guidelines with 30% more load per shelf than conventional chambers

SMART



Exceptionally quiet operation

RELIABLE



Stable climate even at temperatures up to 28 °C below ambient

ECONOMICAL



Lowest energy consumption of its class based on superior Peltier-technology

TECHNICAL DATA


Description	KBF-S ECO 240 UL-120V	KBF-S ECO 720 UL-120V	KBF-S ECO 1020 UL-120V
Performance Data Temperature			
Max. heat compensation at 40 °C [W]	250	400	400
Temperature fluctuation at 40 °C [± K]	0,2	0,3	0,5
Temperature range (max. 28°C below ambient temperature) [°C]*	0...70	0...70	0...70
Temperature variation at 40 °C [± K]	0,1	0,1	0,1
Performance data climate			
Recovery time after 30 seconds door open at 25 °C and 60 % RH [min]	5	7	5
Recovery time after 30 seconds door open at 40 °C and 75 % RH [min]	11	17	15
Humidity range [% RH]	10...80	10...80	10...80
Temperature variation at 25 °C and 60 % RH [± K]	0,1	0,1	0,1
Temperature variation at 40 °C and 75 % RH [± K]	0,2	0,3	0,5
Temperature range (max. 28°C below ambient temperature) [°C]*	5...70	5...70	5...70
Humidity fluctuation at 25 °C and 60 % RH	0,3	0,3	0,4
Humidity fluctuation at 40 °C and 75 % RH	0,3	0,3	0,4
Temperature fluctuation at 25 °C and 60 % RH [± K]	0,1	0,1	0,1
Temperature fluctuation at 40 °C and 75 % RH [± K]	0,1	0,1	0,1
Measures			
Net weight of the unit (empty) [lbs]	322	589	710
Interior volume [cu.ft.]	8.7	24.7	36
Load per rack [lbs]	66	99	99
Permitted load [lbs]	220	331	331
Environment-specific data			
Energy consumption at 40 °C and 75 % RH [Wh/h]	85	130	135
Sound-pressure level [dB(A)]	46	48	49
Fixtures			
Number of shelves (std./max.)	2/9	2/15	2/15
Cat.No.	08-112-054	08-112-055	08-112-056

* With the KBF-S ECO 240, temperature differences of up to 28 °C below the ambient temperature are possible, with the KBF-S ECO 720 and KBF-S ECO 1020, temperature differences of up to 24 °C below the ambient temperature are possible.
The lowest operating temperature for all devices is 0 °C, regardless of the ambient temperature

OPTIONS & ACCESSORIES



Access ports



Qualification documents



Rack



LED strip light accessories

Distributed by Fisher Scientific. Contact us today:

In the United States

Order online: fishersci.com

Call customer service: 1-800-766-7000

In Canada

Order online: fishersci.ca

Call customer service: 1-800-234-7437

 **fisher scientific**
part of Thermo Fisher Scientific