


Upgrade Your Liquid Handling with Corning® Serological Pipets

Made in the USA



To support the changing needs of our customers, Corning has implemented upgrades in the form of increased sterility assurance level, a human DNA-free claim, and availability of extractables data. In addition, we continue to manufacture these products in the US to ensure quality, service, and sustainability.



Made in the USA

Corning serological pipets are proudly manufactured in the United States to strict quality standards. Domestic manufacturing reduces transport emissions and promotes supply assurance.



Human DNA-free

The serological pipets now feature a human DNA-free claim. Pipets will be tested by DNA detection assay per ISO 18385 and found to be free of detectable human DNA. The limit of detection is 10^{-11} g of human genomic DNA.



Extractables data

Extractables analysis is conducted in accordance with USP <665>. Data is available upon customer request.



Sterility Assurance Level (SAL) of 10^{-6}

The serological pipets are sterilized and dosimetrically released per the requirements of ANSI/AAMI/ISO 11137. The Sterility Assurance Level has been increased from a SAL of 10^{-3} to 10^{-6} .

Ordering Information



Individually Wrapped, Clear Plastic Wrap


Fisher Cat. No.	Corning Cat. No.	Capacity (mL)	Graduations (mL)	Negative Grads. (mL)	Color-coded Stripe	Qty/Pk	Qty/Cs
07-200-2	4011	1	1/100	0.2	Yellow	50	1,000
07-200-3	4012	1	1/100	0.2	Yellow	50	200
07-200-7	4021	2	1/100	0.2	Green	50	1,000
07-200-9	4051	5	1/10	2.5	Blue	50	200
07-200-12	4101	10	1/10	3.0	Orange	50	200
07-200-619*	4492	10	1/10	3.0	Orange	50	200
07-200-15	4251	25	2/10	10.0	Red	50	200
07-200-17	4501	50	1/2	10.0	Purple	25	100
07-200-547	4484	100	1	n/a	Aqua	10	100

*Cat. No. 07-200-619 features a wide tip for handling viscous fluids.



Individually Wrapped, Paper/Plastic Wrap

07-200-571	4485	1	1/100	0.2	Yellow	50	1,000
07-200-572	4486	2	1/100	0.2	Green	50	1,000
07-200-573	4487	5	1/10	2.5	Blue	50	200
07-200-574	4488	10	1/10	3.0	Orange	50	200
07-200-575	4489	25	2/10	10.0	Red	25	200
07-200-576	4490	50	1/2	10.0	Purple	25	100
07-200-620	4491	100	1	N/A	Aqua	10	100



Bulk Packed in Bags

07-200-1	4010	1	1/100	0.2	Yellow	50	1,000
07-200-6	4020	2	1/100	0.2	Green	50	1,000
07-200-8	4050	5	1/10	2.5	Blue	50	500
07-200-11	4100	10	1/10	3.0	Orange	50	500
07-200-14	4250	25	2/10	10.0	Red	25	200
07-200-16	4500	50	1/2	10.0	Purple	25	100

Warranty/Disclaimer: Unless otherwise specified, all products are for research use or general laboratory use only.* Not intended for use in diagnostic or therapeutic procedures. Not for use in humans. These products are not intended to mitigate the presence of microorganisms on surfaces or in the environment, where such organisms can be deleterious to humans or the environment. Corning Life Sciences makes no claims regarding the performance of these products for clinical or diagnostic applications. *For a listing of US medical devices, regulatory classifications or specific information on claims, visit www.corning.com/resources.

Corning's products are not specifically designed and tested for diagnostic testing. Many Corning products, though not specific for diagnostic testing, can be used in the workflow and preparation of the test at the customers discretion. Customers may use these products to support their claims. We cannot make any claims or statements that our products are approved for diagnostic testing either directly or indirectly. The customer is responsible for any testing, validation, and/or regulatory submissions that may be required to support the safety and efficacy of their intended application.

CORNING

For a listing of trademarks, visit www.corning.com/clstrademarks. All other trademarks are the property of their respective owners.
© 2023 Corning Incorporated. All rights reserved. 4/23 CLS-LH-379 FISHER

Distributed by Fisher Scientific. Contact us today:

In the United States

Order online: fishersci.com

Call customer service: 1-800-766-7000

In Canada

Order online: fishersci.ca

Call customer service: 1-800-234-7437

 **fisher scientific**
part of Thermo Fisher Scientific

© 2023 Thermo Fisher Scientific Inc. All rights reserved.
Trademarks used are owned as indicated at fishersci.com/trademarks.

BN236024551-NA